


OMNIMATE Signal - series BL/SL 5.08
BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Female header for PCB mounting. The solder pin length is optimised for wave flow soldering.

- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	BLL 5.08/02/180 3.2 SN OR BX
Order No.	1630710000
Version	PCB plug-in connector, female header, closed side, Solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 3.2 mm, tinned, Orange, Box
GTIN (EAN)	4008190204136
Qty.	180 pc(s).
Product data	IEC: 400 V / 23 A UL: 300 V / 15 A
Packaging	Box

Creation date December 25, 2013 11:12:33 AM CET

OMNIMATE Signal - series BL/SL 5.08
BLL 5.08/02/180 3.2 SN OR BX
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data
Dimensions and weights

Net weight	1.97 g
------------	--------

System parameters

Product family	OMNIMATE Signal - series BL/SL 5.08	Mounting onto the PCB	Solder connection
Outgoing elbow	180°	Pitch in mm (P)	5.08 mm
Pitch in inches (P)	0.2 inch	No. of poles	2
Solder pin length (l)	3.2 mm	Pin dimensions	0.4 x 1.00 mm
Can be coded	Yes	Number of solder pins per pole	2
Solder eyelet hole diameter (D)	1.3 mm	Solder eyelet hole diameter tolerance (D)+	0.1 mm
L1 in mm	5.08 mm	L1 in inches	0.2 inch
Insulation resistance	10 ³ Ω	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch

Material data

Insulating material	PBT GF	Colour	Orange
Insulating material group	IIla	UL 94 flammability rating	V-0
CTI	≥ 200	Contact material	Cu-Leg
Contact surface	tinned	Max. relative humidity during storage	80 %

DIN IEC rating data

Rated current, min. no. of poles (Tu=20°C)	23 A	Rated current, max. no. of poles (Tu=20°C)	16 A
Rated current, number of poles (Tu=40°C), min	20 A	Rated current, number of poles (Tu=40°C), max.	14 A
Rated voltage for surge voltage class pollution degree III/3	250 V	Rated impulse voltage for surge voltage classcontamination degree III/3	4 kV
Rated voltage for surge voltage class pollution degree III/2	320 V	Rated impulse voltage for surge voltage classpollution degree III/2	4 kV
Rated voltage for surge voltage class pollution degree II/2	400 V	Rated impulse voltage for surge voltage classpollution degree II/2	4 kV
Short-time withstand current resistance	3 x 1 s with 120 A		

CSA rating data

Institute (CSA)		Rated voltage (Use group B)	300 V
Rated current (use group B)	15 A	Rated voltage (use group D)	300 V
Rated current (use group D)	10 A		

UL 1059 rating data

Institute (UR)		Rated voltage (use group B)	300 V
Rated current (use group B)	15 A	Rated voltage (use group D)	300 V
Rated current (use group D)	10 A		

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Classifications

ETIM 3.0	EC001284	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-04	eClass 6.2	27-26-07-04
eClass 7.1	27-44-04-02		

Notes

Notes

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

Approvals

Approvals



ROHS

Conform


Downloads

CAD Library (P-CAD Format - ASCII) [BLL.zip](#)CAD Library (P-CAD Format - Standard) [BLL.zip](#)[3-D model](#)

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



OMNIMATE Signal - series BL/SL 5.08

BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SL-SMT 5.08/180LF Tape



High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1776364001	PCB plug-in connector,	4032248163472	250 pc(s).	IEC: 400 V / 19 A	Tape
5.08/02/180LF		male header, Solder flange,			UL: 300 V / 15 A	
1.5 SN BK RL		Reflow solder connection,				
		5.08 mm, No. of poles: 2,				
		180°, Solder pin length (l):				
		1.5 mm, tinned, Black, Tape				

SL 5.08/135B



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 17 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL	1605530000	PCB plug-in connector, male	4008190104290	100 pc(s).	IEC: 400 V / 17 A	Box
5.08/02/135B		header, Dovetails for fixing			UL: 300 V / 15 A	
3.2SN OR BX		blocks, Solder connection,				
		5.08 mm, No. of poles: 2,				
		135°, Solder pin length (l):				
		3.2 mm, tinned, Orange,				
		Box				

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SL-SMT 5.08/90LF Tape



High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1775234001	PCB plug-in connector,	4032248 167784 350 pc(s).		IEC: 400 V / 19 A	Tape
5.08/02/90LF		male header, Solder flange,			UL: 300 V / 15 A	
1.5 SN BK RL		Reflow solder connection,				
		5.08 mm, No. of poles: 2,				
		90°, Solder pin length (l):				
		1.5 mm, tinned, Black, Tape				

SLS 5.08/180FI



Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 21.5 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLS	1846210000	PCB plug-in connector,	4032248362493 100 pc(s).		IEC: 400 V / 21.5 A / 0.2 - 2.5 mm ²	Box
5.08/02/180FI		male plug, 5.08 mm, No.			UL: 300 V / 14 A / AWG 26 - AWG 12	
SN OR BX		of poles: 2, 180°, Clamping				
		yoke connection, Clamping				
		range, rated connection,				
		max.: 3.31 mm ² , Box				

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SL 5.08/90B



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL	1510360000	PCB plug-in connector, male	4008190180188	100 pc(s).	IEC: 400 V / 18 A	Box
5.08/02/90B		header, Dovetails for fixing			UL: 300 V / 15 A	
3.2SN OR BX		blocks, Solder connection,				
		5.08 mm, No. of poles: 2,				
		Solder pin length (l): 3.2				
		mm, tinned, Orange, Box				

SL-SMT 5.00/90LF Tape



High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1797750000	PCB plug-in connector,	4032248239757	350 pc(s).	IEC: 400 V / 19 A	Tape
5.00/02/90LF		male header, Solder flange,			UL: 300 V / 15 A	
1.5SN BK RL		Reflow solder connection,				
		5.00 mm, No. of poles: 2,				
		90°, Solder pin length (l):				
		1.5 mm, tinned, Black, Tape				

OMNIMATE Signal - series BL/SL 5.08

BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SLZF 5.08/90B




Male plugs with tension-clamp wire connection. The male plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLZF	1673550000	PCB plug-in connector,	4008190435264	100 pc(s).	IEC: 400 V / 20.5 A / 0.2 - 2.5 mm ²	Box
5.08/02/90B		male plug, 5.08 mm,			UL: 300 V / 15 A / AWG 26 - AWG 12	
SN OR BX		No. of poles: 2, 90°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box				

SLS 5.08/180B



Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 21.5 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLS	1627240000	PCB plug-in connector,	4008190199753	100 pc(s).	IEC: 400 V / 21.5 A / 0.2 - 2.5 mm ²	Box
5.08/02/180B		male plug, 5.08 mm, No.			UL: 300 V / 14 A / AWG 26 - AWG 12	
SN OR BX		of poles: 2, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box				

OMNIMATE Signal - series BL/SL 5.08

BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (conditionally pluggable)

SLZF 5.08/180FI



Male plugs with tension-clamp wire connection. The male plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLZF	1846510000	PCB plug-in connector,	4032248362813	100 pc(s).	IEC: 400 V / 23 A / 0.2 - 2.5 mm ²	Box
5.08/02/180FI		male plug, 5.08 mm,			UL: 300 V / 15 A / AWG 26 - AWG 12	
SN OR BX		No. of poles: 2, 180°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box				

SLDV-THR 5.08/180FLF



High-temperature resistant, double level, laterally offset, male connector with flange or solder flange. 1.5 mm solder pin is suitable for reflow soldering. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLDV-THR	1829130000	PCB plug-in connector,	4032248335824	50 pc(s).	IEC: 400 V / 15 A	Box
5.08/04/180FLF		male header, Flange /			UL: 300 V / 10 A	
1.5SN BK BX		Solder flange, Reflow solder connection, 5.08 mm, No. of poles: 4, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Box				
SLDV-THR	1829010000	PCB plug-in connector,	4032248335701	50 pc(s).	IEC: 400 V / 15 A	Box
5.08/04/180FLF		male header, Flange /			UL: 300 V / 10 A	
3.2SN BK BX		Solder flange, Reflow solder connection, 5.08 mm, No. of poles: 4, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Box				

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SL-SMT 5.08/180LF Box



High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT 5.08/02/180LF 1.5SN BK BX	1776362001	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Box	4032248159147	100 pc(s).	IEC: 400 V / 19 A UL: 300 V / 15 A	Box
SL-SMT 5.08/02/180LF 3.2SN BK BX	1838440000	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Box	4032248348503	100 pc(s).	IEC: 400 V / 19 A UL: 300 V / 15 A	Box

SL-SMT 5.08/90F Box



High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT 5.08/02/90F 3.2SN BK BX	1837630000	PCB plug-in connector, male header, Flange, Reflow solder connection, 5.08 mm, No. of poles: 2, 90°, Solder pin length (l): 3.2 mm, tinned, Black, Box	4032248347445	100 pc(s).	IEC: 400 V / 19 A UL: 300 V / 15 A	Box

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SL-SMT 5.08/90LF Box




High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT 5.08/02/90LF 3.2SN BK BX	1780410000	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 5.08 mm, No. of poles: 2, 90°, Solder pin length (l): 3.2 mm, tinned, Black, Box	4032248165735	100 pc(s).	IEC: 400 V / 19 A UL: 300 V / 15 A	Box
SL-SMT 5.08/02/90LF 1.5SN BK BX	1775232001	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 5.08 mm, No. of poles: 2, 90°, Solder pin length (l): 1.5 mm, tinned, Black, Box	4032248157211	100 pc(s).	IEC: 400 V / 19 A UL: 300 V / 15 A	Box

SL-SMarT 5.0x/180 Tape



High-temperature resistant male header for side-by-side mounting. Packed in tape with 1.5 mm solder pin. Optimised for automatic assembly and suitable for reflow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMART 5.0X/02/180 1.5SN BK RL	1812450000	PCB plug-in connector, male header, open side, Reflow solder connection, 5.00 mm, No. of poles: 2, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Tape	4032248294039	270 pc(s).	IEC: 400 V / 16.5 A UL: 300 V / 15 A	Tape

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SLS 5.08/180F




Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 21.5 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLS	1846360000	PCB plug-in connector,	4032248362066	100 pc(s).	IEC: 400 V / 21.5 A / 0.2 - 2.5 mm ²	Box
5.08/02/180F		male plug, 5.08 mm, No.			UL: 300 V / 14 A / AWG 26 - AWG 12	
SN OR BX		of poles: 2, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box				

SLZF 5.08/180B



Male plugs with tension-clamp wire connection. The male plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLZF	1710210000	PCB plug-in connector,	4008190319526	100 pc(s).	IEC: 400 V / 23 A / 0.2 - 2.5 mm ²	Box
5.08/02/180B		male plug, 5.08 mm,			UL: 300 V / 15 A / AWG 26 - AWG 12	
SN OR BX		No. of poles: 2, 180°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box				

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SL-SMT 5.08/180F Box



High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1837320000	PCB plug-in connector, male	4032248345915	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/180F		header, Flange, Reflow			UL: 300 V / 15 A	
1.5SN BK BX		solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Box				
SL-SMT	1837860000	PCB plug-in connector, male	4032248347674	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/180F		header, Flange, Reflow			UL: 300 V / 15 A	
3.2SN BK BX		solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Box				

SLT 5.08B



Male plugs with screw TOP wire connection. The male plug provides space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 16 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLT	1611710000	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, TOP connection, Clamping range, rated connection, max.: 2.5 mm ² , Box	4008190192594	100 pc(s).	IEC: 400 V / 16 A / 0.2 - 2.5 mm ²	Box
5.08/02/180B					UL: 300 V / 15 A / AWG 26 - AWG 14	
SN OR BX						

OMNIMATE Signal - series BL/SL 5.08

BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SLDV-THR 5.08/180F




High-temperature resistant, double level, laterally offset, male connector with flange or solder flange. 1.5 mm solder pin is suitable for reflow soldering. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLDV-THR	1828770000	PCB plug-in connector, male	4032248335442	50 pc(s).	IEC: 400 V / 15 A	Box
5.08/04/180F		header, Flange, Reflow			UL: 300 V / 10 A	
3.2SN BK BX		solder connection, 5.08 mm, No. of poles: 4, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Box				
SLDV-THR	1828890000	PCB plug-in connector, male	4032248335589	50 pc(s).	IEC: 400 V / 15 A	Box
5.08/04/180F		header, Flange, Reflow			UL: 300 V / 10 A	
1.5SN BK BX		solder connection, 5.08 mm, No. of poles: 4, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Box				

SL 5.00/90B



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL	1580860000	PCB plug-in connector, male	4008190054489	100 pc(s).	IEC: 400 V / 18 A	Box
5.00/02/90B		header, Dovetails for fixing			UL: 300 V / 15 A	
3.2SN OR BX		blocks, Solder connection, 5.00 mm, No. of poles: 2, 90°, Solder pin length (l): 3.2 mm, tinned, Orange, Box				


OMNIMATE Signal - series BL/SL 5.08

BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SL-SMaRT 5.0x/90 Tape



High-temperature resistant male header for side-by-side mounting. Packed in tape with 1.5 mm solder pin. Optimised for automatic assembly and suitable for reflow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMaRT	1812430000	PCB plug-in connector, male	4032248294015	350 pc(s).	IEC: 400 V / 16.5 A	Tape
5.0X/02/90		header, open side, Reflow			UL: 300 V / 15 A	
1.5SN BK RL		solder connection, 5.00 mm, No. of poles: 2, 90°, Solder pin length (l): 1.5 mm, tinned, Black, Tape				

SL 5.08/180B



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL	1519560000	PCB plug-in connector, male	4008190083892	100 pc(s).	IEC: 400 V / 18 A	Box
5.08/02/180B		header, Dovetails for fixing			UL: 300 V / 15 A	
3.2SN OR BX		blocks, Solder connection, 5.08 mm, No. of poles: 2, Solder pin length (l): 3.2 mm, tinned, Orange, Box				

OMNIMATE Signal - series BL/SL 5.08

BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

SL-SMT 5.00/90LF Box



High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1797230000	PCB plug-in connector,	4032248238019	100 pc(s).	IEC: 400 V / 19 A	Box
5.00/02/90LF		male header, Solder flange,			UL: 300 V / 15 A	
1.5SN BK BX		Reflow solder connection,				
		5.00 mm, No. of poles: 2,				
		90°, Solder pin length (l):				
		1.5 mm, tinned, Black, Box				
SL-SMT	1840350000	PCB plug-in connector,	4032248351091	100 pc(s).	IEC: 400 V / 19 A	Box
5.00/02/90LF		male header, Solder flange,			UL: 300 V / 15 A	
3.2SN BK BX		Reflow solder connection,				
		5.00 mm, No. of poles: 2,				
		90°, Solder pin length (l):				
		3.2 mm, tinned, Black, Box				

SLZF 5.08/270B



Male plugs with tension-clamp wire connection. The male plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLZF	1706140000	PCB plug-in connector,	4032248113996	100 pc(s).	IEC: 400 V / 20.5 A / 0.2 - 2.5 mm ²	Box
5.08/02/270B		male plug, 5.08 mm,			UL: 300 V / 15 A / AWG 26 - AWG 12	
SN OR BX		No. of poles: 2, 270°,				
		Tension clamp connection,				
		Clamping range, rated				
		connection, max.: 3.31				
		mm ² , Box				

OMNIMATE Signal - series BL/SL 5.08
BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)
SLZF 5.08/180F


Male plugs with tension-clamp wire connection. The male plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLZF	1846930000	PCB plug-in connector,	4032248363100	100 pc(s).	IEC: 400 V / 23 A / 0.2 - 2.5 mm ²	Box
5.08/02/180F		male plug, 5.08 mm,			UL: 300 V / 15 A / AWG 26 - AWG 12	
SN OR BX		No. of poles: 2, 180°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box				

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

SL-SMT 5.08/180G Tape




High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1820170000	PCB plug-in connector, male	4032248315680	250 pc(s).	IEC: 400 V / 19 A	Tape
5.08/02/180G		header, closed side, Reflow			UL: 300 V / 15 A	
1.5 SN BK RL		solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Tape				

SLZF 5.08/180



Male plugs with tension-clamp wire connection. The male plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLZF	1709370000	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190390150	100 pc(s).	IEC: 400 V / 23 A / 0.2 - 2.5 mm ² UL: 300 V / 15 A / AWG 26 - AWG 12	Box
5.08/02/180 SN OR BX						
SLZF	1709600000	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190318901	100 pc(s).	IEC: 400 V / 23 A / 0.2 - 2.5 mm ² UL: 300 V / 15 A / AWG 26 - AWG 12	Box
5.08/02/180 SN BK BX						


OMNIMATE Signal - series BL/SL 5.08

BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

SLDF 5.08



Male connector for through-panel mounting with optional locking function. Internal connection as flat-blade or solder connection. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLDF 5.08 L/F 2 SN BK BX	1635740000	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Flat- blade connection, Solder connection, Box	4008190264161	100 pc(s).	IEC: 400 V / 15 A UL: 300 V / 10 A	Box
SLDF 5.08 L/F 2 SN OR BX	1599130000	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Flat- blade connection, Solder connection, Box	4008190175931	100 pc(s).	IEC: 400 V / 15 A UL: 300 V / 10 A	Box

SL 5.08/180



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL 5.08/02/180 3.2SN OR BX	1517260000	PCB plug-in connector, male header, open side, Solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 3.2 mm, tinned, Orange, Box	4008190034795	100 pc(s).	IEC: 400 V / 18 A UL: 300 V / 15 A	Box

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

SL-SMT 5.08/180 Tape



High-temperature-resistant, straight, open ended male header. Packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1821100000	PCB plug-in connector, male	4032248319749	250 pc(s).	IEC: 400 V / 19 A	Tape
5.08/02/180		header, open side, Reflow			UL: 300 V / 15 A	
1.5 SN BK RL		solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Tape				

SL-SMT 5.08/90G Box



High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1780180000	PCB plug-in connector, male	4032248165506	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/90G		header, closed side, Reflow			UL: 300 V / 15 A	
3.2SN BK BX		solder connection, 5.08 mm, No. of poles: 2, 90°, Solder pin length (l): 3.2 mm, tinned, Black, Box				
SL-SMT	1775002001	PCB plug-in connector, male	4032248156023	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/90G		header, closed side, Reflow			UL: 300 V / 15 A	
1.5SN BK BX		solder connection, 5.08 mm, No. of poles: 2, 90°, Solder pin length (l): 1.5 mm, tinned, Black, Box				

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

SL-SMT 5.08/90 Box



High-temperature-resistant, 90° angled, open male header
Packed in box or tape. In tape with 1.5 mm solder pin
optimised for automatic assembly. 3.2 mm solder pin
suitable for reflow and wave soldering. These male
connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1774762001	PCB plug-in connector, male	4032248155699	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/90		header, open side, Reflow			UL: 300 V / 15 A	
1.5SN BK BX		solder connection, 5.08				
		mm, No. of poles: 2, 90°,				
		Solder pin length (l): 1.5				
		mm, tinned, Black, Box				
SL-SMT	1779950000	PCB plug-in connector, male	4032248165278	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/90		header, open side, Reflow			UL: 300 V / 15 A	
3.2SN BK BX		solder connection, 5.08				
		mm, No. of poles: 2, 90°,				
		Solder pin length (l): 3.2				
		mm, tinned, Black, Box				

SLD 5.08/180G



2-tier male header with parallel pin arrangement. The
solder pin length is optimised for wave flow soldering.
The pin headers provide space for labelling and can be
coded.

- 400 V (IEC) / 300 V (UL)
- 11 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLD	1602390000	PCB plug-in connector, male	4008190180539	50 pc(s).	IEC: 400 V / 11 A	Box
5.08/04/180G		header, closed side, Solder			UL: 300 V / 10 A	
3.2SN OR BX		connection, 5.08 mm, No.				
		of poles: 4, 180°, Solder pin				
		length (l): 3.2 mm, tinned,				
		Orange, Box				

OMNIMATE Signal - series BL/SL 5.08

BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

SLD 5.08/90G



2-tier male header with parallel pin arrangement. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 11 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SLD	1601790000	PCB plug-in connector, male	4008190055752	50 pc(s).	IEC: 400 V / 11 A	Box
5.08/04/90G		header, closed side, Solder connection, 5.08 mm, No. of poles: 4, 90°, Solder pin length (l): 3.2 mm, tinned,			UL: 300 V / 10 A	
3.2SN OR BX		Orange, Box				

SL 5.08/135



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 17 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL	1603060000	PCB plug-in connector, male	4008190095512	100 pc(s).	IEC: 400 V / 17 A	Box
5.08/02/135		header, open side, Solder connection, 5.08 mm, No. of poles: 2, 135°, Solder pin length (l): 3.2 mm, tinned,			UL: 300 V / 15 A	
3.2SN OR BX		Orange, Box				

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

SL-SMT 5.08/180 Box



High-temperature-resistant, straight, open ended male header. Packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1775522001	PCB plug-in connector, male	4032248157549	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/180		header, open side, Reflow solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Box			UL: 300 V / 15 A	
1.5SN BK BX						
SL-SMT	1837980000	PCB plug-in connector, male	4032248348046	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/180		header, open side, Reflow solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Box			UL: 300 V / 15 A	
3.2SN BK BX						

SL 5.00/90



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL	1625990000	PCB plug-in connector, male	4008190197292	100 pc(s).	IEC: 400 V / 18 A	Box
5.00/02/90		header, open side, Solder connection, 5.00 mm, No. of poles: 2, 90°, Solder pin length (l): 4.5 mm, tinned, Black, Box			UL: 300 V / 15 A	
4.5SN BK BX						
SL	1571130000	PCB plug-in connector, male	4008190156121	100 pc(s).	IEC: 400 V / 18 A	Box
5.00/02/90		header, open side, Solder connection, 5.00 mm, No. of poles: 2, 90°, Solder pin			UL: 300 V / 15 A	
3.2SN OR BX						

OMNIMATE Signal - series BL/SL 5.08

BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

length (l): 3.2 mm, tinned,
 Orange, Box

SL 5.08/90



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL	1508060000	PCB plug-in connector, male	4008190189006	100 pc(s).	IEC: 400 V / 18 A	Box
5.08/02/90		header, open side, Solder connection, 5.08 mm, No. of poles: 2, 90°, Solder pin length (l): 3.2 mm, tinned, Orange, Box			UL: 300 V / 15 A	
3.2SN OR BX						

SL-SMT 5.08/180G Box



High-temperature-resistant male header, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1775922001	PCB plug-in connector, male	4032248158911	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/180G		header, closed side, Reflow solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Box			UL: 300 V / 15 A	
1.5SN BK BX						
SL-SMT	1838210000	PCB plug-in connector, male	4032248348275	100 pc(s).	IEC: 400 V / 19 A	Box
5.08/02/180G		header, closed side, Reflow solder connection, 5.08 mm, No. of poles: 2, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Box			UL: 300 V / 15 A	
3.2SN BK BX						

OMNIMATE Signal - series BL/SL 5.08 BLL 5.08/02/180 3.2 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmüller.com

Mating connector (fully pluggable)

SL-SMT 5.08/90 Tape



High-temperature-resistant, 90° angled, open male header
Packed in box or tape. In tape with 1.5 mm solder pin
optimised for automatic assembly. 3.2 mm solder pin
suitable for reflow and wave soldering. These male
connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1821160000	PCB plug-in connector, male	4032248319800	350 pc(s).	IEC: 400 V / 19 A	Tape
5.08/02/90		header, open side, Reflow			UL: 300 V / 15 A	
1.5 SN BK RL		solder connection, 5.08 mm, No. of poles: 2, 90°, Solder pin length (l): 1.5 mm, tinned, Black, Tape				

SL-SMT 5.08/90G Tape



High-temperature-resistant male header, packed in box
or tape. In tape with 1.5 mm solder pin optimised for
automatic assembly. 3.2 mm solder pin suitable for
reflow and wave soldering. These male connectors
provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SL-SMT	1821140000	PCB plug-in connector, male	4032248319787	350 pc(s).	IEC: 400 V / 19 A	Tape
5.08/02/90G		header, closed side, Reflow			UL: 300 V / 15 A	
1.5 SN BK RL		solder connection, 5.08 mm, No. of poles: 2, 90°, Solder pin length (l): 1.5 mm, tinned, Black, Tape				