

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	KASP
Product Range	Heavy Duty Combination Padlock
Catalogue number	117
Date	19/03/2009

Range Description Resettable combination padlocks		 		
Features • Hardened Steel Shackle - Extra protection against hacksaw & cropping attacks • Double Bolted Locking Mechanism - Extra strength to resist torsion & pull attacks • Anti Manipulation Locking System - Protects against manipulation attack • 4 Dial Resettable Combination - Resettable combination for added convenience & security • Rust Free Internal Components - Extra resistance against corrosion The padlock is supplied display packed, in sealed blister packs.				
Item Number	Item Description			
K11750D	Heavy Duty Combination Padlock 50mm – display packed	5013969901771	83011000	6

Technical product information	Body – Die Cast, Chrome plated Shackle - Hardened steel, Chrome plated Locking mechanism - Double bolted, 4 dial combination locking mechanism featuring an anti-manipulation locking system to prevent intelligent manipulation attack.
-------------------------------	--

To open the padlock:

1) Using the correct combination code, open the padlock by aligning the dial wheels with the indicators on the lock body (pre-set factory combination code 0-0-0-0) and depress the shackle

To lock the padlock:

1) Whilst in the open position, scramble the dial wheels and depress the shackle into the body of the padlock until it locks

To reset the lock to a combination of your choice:

1) Open the padlock using the preset combination code

2) Insert the change key into the keyhole on the side of the padlock

3) Firmly press the key into the keyhole and turn 90 degrees clockwise or anti-clockwise. *[IMPORTANT: Ensure the change key is fully depressed to avoid losing the combination]*

4) With the change key held at 90 degrees, reset the dials wheels to a combination of your choice (we recommend that you record your new combination code and store it in a safe place)

5) With your new combination code set, turn the change key through 90 degrees back to its original position and withdraw it from the key hole

6) Lock the padlock by scrambling the dial wheels and depressing the shackle into the body of the padlock until it locks

Security rating:

Type	Security rating
K11750D	6

Shackle Dimensions:

Dimensions mm	Shackle			Body
	Dia	Internal width	Internal height	Width
K11750D	8	25	25	50

Use environment - Normal outdoor use ✓✓

Recommended applications- Lockers, sheds, gates, garages

Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered
Country of origin	Taiwan

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K11750D	50	25	75	246	118	27	186	290

	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K11750D	130	200	115	1855		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K11750D	36	Blister	8	Backing card			104	Box