


Product Data Sheet

Part No. GT-111P Non-Washable Type


DIMENSIONS



UNIT : mm
TOLERANCE : ±0.3
HOUSING MATERIAL : PPO

Type	Unit	
Color		Black
Rated Voltage	(V)	1.5
Operating Voltage	(V)	1-4
Current Consumption	(mA)	MAX.10
Coil Resistance	(Ω)	50±7.5
Sound Output (Min)	(dB)	80
Resonance Frequency	(Hz)	2048
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-30~+70
Weight	(g)	2
Terminal		PIN TYPE
Dimension	mm	12 x H8.5
*applied voltage: Rated Voltage, 1/2 duty, square wave		
*distance for measurement: 10cm		

FREQUENCY RESPONSE



Product Data Sheet

