


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		E1	REVISED PER ECO-12-003798	29FEB12	KH	DR



AMP WIRE RANGE	UL Listed FILE E13288	LR7189 Certified
4/0 AWG SOLID OR STRANDED	4/0 AWG STRANDED 4	4/0 AWG SOLID OR STRANDED 4


- 1
- STAMP AMP 4/OW* 200 APPROX AS SHOWN

2

3

4

5

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 030CT97		 TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: SEE TABLE	DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK MJ SPICER 060CT97	NAME TERMINAL, RING TONGUE, FLAG, SOLISTRAND			
			APVD JL MECKLEY 060CT97							
			PRODUCT SPEC —							
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE		MATERIAL	FINISH SEE TABLE	APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 96.3–117.0mm ² [190,000–231,000] CIR MILS SOLID OR STRANDED				WEIGHT —	A3	00779	C=321259	—
CUSTOMER DRAWING							SCALE 2:1		SHEET 1 OF 1	REV E1