

2365/2380 SERIAL MATRIX PRINTERS



Print speeds up to 1000 cps

Up to 9-part forms

**Full range of automatic features
to minimize user intervention**

**Ideal for 'On Demand' applications
with zero tear for no wasted forms**

Straight through paper path for easy forms loading

Parallel and Ethernet (10/100BaseT) standard

Ethernet IPDS

Compatible with a wide range of operating systems

RUGGED FOR HEAVY DUTY OPERATION

HIGH SPEED OPERATION

The 2365 and 2380 printers are rugged and powerful high speed serial matrix printers for heavy duty operation under the most extreme conditions. The 24-pin print head provides crisp, sharp, dark and absolutely legible output.

EXCELLENT VALUE

Low running costs and durability in the harshest of print environments make these products excellent value for money.

Fully automated operation, coupled with the straight through paper path, allows ease of use and virtually eliminates errors caused by user intervention. These products are well matched to Microsoft Windows applications, and highly compatible with other host operation environments including legacy systems.

Available Configuration.....**2365:** Available in 3 configurations
2380: Available in 2 configurations

2365/2380 SERIAL MATRIX PRINTERS

Print Speed	2365: At 10, 12, 15 cpi: high speed draft 650, 800, 900; draft 600, 720, 900, NLQ 200, 240, 300, LQ 100, 120, 150 2380: At 10, 12, 15 cpi: high speed draft 800, 1000, 1000; draft 667, 800, 1000; NLQ 222, 267, 333; LQ 111,133,167	Power Consumption	2365: 60 watts operating, max 18 watts stand-by 2380: 70 watts operating, max 18 watts stand-by
Print Method	Serial impact	Compliance	ENERGY STAR® qualified, Ozone-free, RoHS, Microsoft, ISO-compliant
Resolution	360 x 360 dpi	Workload	2365: Up to 48,000 pages per month 2380: Up to 50,000 pages per month
Character Density	5, 6, 7.5, 8.6, 10, 12, 15, 17.1, 20 cpi (Emulation dependent)	Reliability MTBF	12,500 hours @ 25% duty cycle
Line Density	2, 3, 4, 6, 8, 12 lpi	Drivers	Windows 2000, XP, Vista, Windows 7, Server 2003, Server 2008; SAP
Printhead Life	750 million characters	Temperature	Operating: +10°C to +35°C; 50°F to 95°F; Storage: +5°C to +45°C; 41°F to 113°F
Printhead Type	24 wire	Humidity	Operating 15% to 75%; Storage 5% to 95% (relative humidity)
Memory	128kB	Acoustic	2365: 59 dBA (ISO 7779) 2380: 57 dBA (ISO 7779)
Standard Connectivity	Bi-directional parallel plus Ethernet 10/100BaseT with 128kb buffer	Warranty	For warranty information go to www.tallygenicom.com
Optional Connectivity	RS232 serial, Twinax/Coax, Ethernet IPDS	Option 1	Pedestal cabinet, paper basket
Standard Emulation	IBM Proprinter XL24e, Epson LQ-2550, Epson LQ-2170 (ESC P/2), Genicom ANSI, MTPL	Note	For OCR applications it is recommended that your readers are tested with print samples supplied by TallyGenicom prior to purchase. Paper is a highly variable medium and should be tested prior to purchase. The quoted consumable life is the average for the printer when used under normal operating conditions.
Optional Emulation	PCL3		
Fonts	HS Draft, Draft, Copy Draft, Courier, Roman, Sans Serif, Prestige, Script, Orator, Gothic, Souvenir, Kix/Royal, OCR A, OCR B, 22 Bar Codes and scalable LCP fonts. Intelligent Mail Barcode		
Consumables	20 million characters		
STD Paper Handling	Front insertion, push tractor with paper parking and AGA; 2nd rear push tractor (2380-2T only)		
Optional Paper Handling	Additional front push tractor with paper parking and AGA		
Number of Copies	2365: Original + 6 (7-part forms); with high impact print head model - original +8 (9 part forms) 2380: Original + 5 (6-part forms); original +4 (5-part forms) for rear tractor of 2380-2T		
Paper Type	Continuous		
Paper Weight	60 to 120 gm2 continuous forms		
Paper Size	Width: 3-16.5"; Length: continuous forms 3-22"		
Printable Area	Up 10 13.6" width		
Physical Weight	2365: 42 lbs. (19kg) 2380: 45.6 lbs. (20.7kg)		
Physical Size	2365: 11" x 24.6" x 17" (280mm x 623mm x 432mm) 2380: 24.5" x 11" x 17" (623mm x 280mm x 432mm)		
Power Voltage	120V/230V		

