


MICRO SWITCH
 FREEPORT ILLINOIS U S A
 A DIVISION OF HONEYWELL
 FED MFG CODE 9183E

**SWITCH - TOGGLE
 FLUSH KEY**

CATALOG LISTING
2TPI SERIES
 CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CATALOG LISTING	CIRCUIT MADE WITH BUTTON DEPRESSED ON			ELECTRICAL DATA
	LUG SIDE (1-2, 4-5)	CENTER (1-2, 4-5)	OPPOSITE LUG (2-3, 5-6)	
2TPI-1	ON	OFF	ON	L191 15A 125, <u>250</u> , 277 VAC 1/2HP 125 VAC 1HP <u>250</u> , 277 VAC 5A 125 VAC "L"
2TPI-2	OFF	NONE	ON	
2TPI-3	ON	NONE	ON	
2TPI-21	NONE	OFF	ON	
2TPI-31	NONE	ON	ON	L192 10A 125, <u>250</u> , 277 VAC 1/4HP 125 VAC, 1/2HP <u>250</u> , 277 VAC 3A 125 VAC "L"
2TPI-4	MOM OFF	NONE	ON	
2TPI-5	MOM ON	OFF	ON	
2TPI-6	MOM ON	NONE	OFF	
2TPI-7	MOM ON	OFF	MOM ON	
2TPI-8	MOM ON	NONE	ON	
(A)	NONE	ON	MOM ON	
2TPI-61	MOM ON	OFF	NONE	



- NOTES
 1 - SWITCH WILL WITHSTAND TEMPERATURE OF 160°F
 2 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
 3 SCREWS FURNISHED UNASSEMBLED
 4 APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS

CATALOG LISTING
2TPI SERIES CHART 1
 PAGE 1 OF 1
 ISSUE **4**
 REVISIONS
 A CO-93153 JJA 5 MAY 99
 B C094412 DLM 13 OCT 99
 C 202714 JAH 30 MAR 01
 CHECK KAG 7 JUL 94
 DRAWN TSM 9 JUN 94
 RASTER
 2TPI SERIES
 REPLACES CO-78497
 RELEASE NO

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
 APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:

NO. PLACES	SI METRIC	TOL.	US CUSTOMARY	TOL.
NO PLACES	mm	1/64	in	0.015
ONE PLACE	mm	0.075	in	0.003
TWO PLACES	mm	0.010	in	0.0005
THREE PLACES	mm	0.002	in	0.0001

DESIGN UNITS SI METRIC US CUSTOMARY

WEIGHT .14 LB EST