

AkroBins®



- Control inventories, shorten assembly times, and minimize parts handling.
- Heavy-duty bins securely stack atop each other, sit on shelving, and hang from Akro-Mils racks, panels, rails, and carts.
- Molded of high-density polypropylene, AkroBins are unaffected by weak acids and alkalis.
- Sturdy, one-piece construction is water, rust, and corrosion-proof.
- Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty.
- Autoclavable up to 250° F.
- Available in 12 sizes and 4 colors: Red, Yellow, Blue, and Stone.



Anti-slide stop prevents stacked bins from shifting forward

Full-width hanger lip supports bin on hanging system




Curved-bottom hopper front makes it easy to retrieve small parts

Large front label slot allows larger bar code scanning

Extra-wide stacking ledge saves space and prevents spills

Reinforced side ribs add strength & prevent spreading when stacked



30270



30235



30239



30230



30210

AkroBins

When compared to the competition, AkroBins:

- Support more weight when stacked.
- Handle more abuse.
- Hold more weight without cracking.




Model No.	Outside Dimensions						Inside Dimensions										Bin Load Capacity On Rack**	Ctn. Qty.
	Inches			mm			Inches				mm							
	L	W	H	L	W	H	L	W	H	X	L	W	H	X				
30210	5⅜	4⅞	3	137	105	76	4¾	3⅞	2⅜⅙	4	120	87	71	102	10 lbs.	24		
30220	7⅜	4⅞	3	187	105	76	6¾	3⅞	2⅜⅙	6	171	87	71	152	10 lbs.	24		
30224	10⅞	4⅞	4	276	105	102	10¼	3⅞	3¾	9	260	87	95	229	30 lbs.	12		
30230	10⅞	5½	5	276	140	127	10¼	4⅜	4¾	9	260	111	121	229	30 lbs.	12		
30234	14⅜	5½	5	375	140	127	14⅞	4⅜	4¾	12⅜⅙	357	111	121	325	50 lbs.	12		
30235	10⅞	11	5	276	279	127	10¼	10	4¾	9	260	254	121	229	50 lbs.	6		
30239	10⅜	8¼	7	273	210	178	10	6⅞	6¾	8	254	167	171	203	50 lbs.	6		
30240	14⅜	8¼	7	375	210	178	14	6⅞	6¾	12	356	167	171	305	60 lbs.	12		
30250	14⅜	16½	7	375	419	178	14	14¾	6¾	12	356	375	171	305	75 lbs.	6		
30255	10⅞	16½	5	276	419	127	9¾	15	4¾	8½	248	381	121	216	60 lbs.	6		
30265*	18	8¼	9	457	210	229	17⅞	6¾	8¼	14½	435	171	210	368	N/A	6		
30270*	18	16½	11	457	419	279	17⅞	14¾	10¼	13¾	435	375	260	349	N/A	3		

One color per carton: Specify Red, Blue, Yellow, or Stone.

*Note 30265 and 30270 are not designed for use with hanging systems.

** CAUTION: When using bins with hanging systems, do not exceed the weight capacity for the rack which may be less than the total sum of bin capacities.

Accessories:



Dividers

Lengthwise dividers keep items separated in the bin.



Bin Lids*

*"See-through" crystal styrene lids keep contents dust-free and protected.

Dividers

Model No.	Fits AkroBins	Pkg. Qty.
40210	30210 (1)	6
40220	30220 (1)	6
40230	30230 (1), 30235 (3)	6
40239	30239 (1)	6
40245	30240 (1), 30250 (1)	6
40265	30265 (1)	6
40270	30270 (3)	6

(Max. # of dividers)

*30224, 30255, 30234 no dividers available.

Bin Lids

Model No.	Fits AkroBins	Ctn. Qty.
30211	30210	24
30221	30220	24
30231	30230	12
30236	30235	6

*Assembly required – hinge pins included.

Super-Size AkroBins & Dollies



Available in 5 sizes and 3 colors: Red, Yellow, and Blue.



30280



30281



30282



30283



30290



AkroBin solid steel Dollies (Model No. RU842HR2018 & RU842HR2918) are available for efficient parts transport.

- Control inventories, shorten assembly times, and minimize parts handling.
- Heavy-duty bins securely stack atop each other, or sit on shelving.
- Molded of high-density polypropylene, AkroBins are unaffected by weak acids and alkalis.
- Sturdy, one-piece construction is water, rust, and corrosion-proof.
- Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty.
- Autoclavable up to 250° F.



Extra-wide stacking ledge saves space and prevents spills

AkroBins can be used alone or stacked together for high-density storage

Anti-slide stop prevents stacked bins from shifting forward



Easy to carry with large handle molded onto back of bin

Large label area on front of bin

Curved-bottom hopper front makes it easy to retrieve small parts

Reinforced side ribs add strength and prevent spreading when stacked


Super-Sized AkroBins

Model No.	Outside Dimensions						Inside Dimensions								Max. Capacity Per Bin	Stacking Capacity /=Qty. Stacked	Ctn. Qty.
	Inches			mm			Inches				mm						
	L	W	H	L	W	H	L	W	H	X	L	W	H	X			
30280	20	12 ³ / ₈	6	508	314	152	16 ⁷ / ₈	10 ¹¹ / ₁₆	5 ³ / ₈	15 ¹ / ₂	429	271	137	394	100lbs.	40lb./10	4
30281	20	12 ³ / ₈	8	508	314	203	16 ⁷ / ₈	10 ¹¹ / ₁₆	7 ³ / ₈	15 ¹ / ₂	429	271	187	394	150lbs.	50lb./7	3
30282	20	12 ³ / ₈	12	508	314	305	16 ⁷ / ₈	10 ¹¹ / ₁₆	11 ³ / ₈	15 ¹ / ₂	429	271	289	394	200lbs.	60lb./5	2
30283	20	18 ³ / ₈	12	508	467	305	16 ⁷ / ₈	16 ⁹ / ₁₆	11 ³ / ₈	15 ¹ / ₂	429	421	289	394	300lbs.	150lb./5	1
30290	29 ¹ / ₄	18 ³ / ₈	12	743	467	305	26 ¹ / ₈	16 ⁹ / ₁₆	11 ³ / ₈	24 ³ / ₄	664	421	289	629	300lbs.	150lb./5	1

One color per carton: Specify Red, Blue, or Yellow. Not recommended to hang on rack or panel systems.

Dollies

Model No.	Dimensions			Ctn. Qty.	Capacity Lbs.	Casters
	L	W	H			
RU842HR2018	20"	18 ³ / ₈ "	3 ¹ / ₂ "	1	500	2" Polyolefin
RU842HR2918	29 ¹ / ₄ "	18 ³ / ₈ "	3 ¹ / ₂ "	1	500	2" Polyolefin



Stak-N-Store Bins



- The perfect way to organize heavy, bulky items.
- Bins stack to form tall, stable storage arrangements on floors or standard industrial shelving.
- 75 lb. weight capacity.
- Color: Gray, Red, Blue.



Small Stak-N-Store bins (13014) fit 3 across on standard 36" shelving. Medium Stak-N-Store bins (13018) fit 2 across on standard 36" shelving. See Shelving Systems on page 11.

Large comfort grip handles

Large radius corners and a curved upper lip add strength

Side ribs insure stability when stacked

Wide-hopper front allows easy access to bulky items



Stack bins together to form a storage system.




13014



13018



13017



Stak-N-Store Bins

Model No.	Outside Dimension					Capacity Cu. Ft.	Ctn. Qty.
	L	Inches W	H	L	mm W		
13014	17½	10⅞	12½	445	276	.98	4
13017	15¼	19⅞	12⅞	387	505	1.7	3
13018	17½	16½	12½	445	419	1.6	2

Order in carton quantities.

Shelf Bins



Shelf bins tilt out for complete access to contents.


- Shelf Bins outlast corrugated bins – paying for themselves in reduced replacement costs.
- Superior construction allows Shelf Bins to be fully loaded without bulging or cracking.
- Durable polypropylene bins provide an attractive, neat appearance.
- Works with 12", 18", and 24" deep shelving, or vertical storage and retrieval units.
- One-piece construction is waterproof and unaffected by grease or oil.
- Available in 13 sizes and 3 colors: Red, Yellow, and Blue.

Wide hopper front allows easy access


Built-in rear hanglock allows bin to tilt out for complete access

Molded-in label holder identifies contents

Optional dividers increase versatility




30120



30150




30158



30124




30164



30174


Shelf Bins



Model No.	Outside Dimension						Inside Dimension						Ctn Qty.	Cups Per Bin		Optional Divider
	Inches			mm			Inches			mm				Small 30101	Large 30102	
	L	W	H	L	W	H	L	W	H	L	W	H				
12" Shelf Bin																
30110	11½	2¾	4	295	70	102	10¼	1⅝	4	260	41	102	24	3	-	None
30120	11½	4⅛	4	295	105	102	10¼	3	4	260	76	102	24	5	2	40120
30130	11½	6⅞	4	295	168	102	10¼	5½	4	260	140	102	12	9	4	40130
30150	11½	8¾	4	295	219	102	10¼	7⅞	4	260	181	102	12	11	4	40150
30170	11½	11⅛	4	295	283	102	10¼	10	4	260	254	102	12	15	6	40170
18" Shelf Bin																
30128	17⅞	4⅛	4	454	105	102	16½	3	4	419	76	102	12	8	3	40120
30138	17⅞	6⅞	4	454	168	102	16½	5½	4	419	140	102	12	15	6	40130
30158	17⅞	8¾	4	454	213	102	16½	7⅞	4	419	181	102	12	15	6	40150
30178	17⅞	11⅛	4	454	283	102	16½	10	4	419	254	102	12	25	12	40170
24" Shelf Bin																
30124	23⅝	4⅛	4	600	105	102	22⅞	3	4	562	76	102	12	11	4	40120
30164	23⅝	6⅞	4	600	168	102	22⅞	5½	4	562	140	102	6	21	8	40130
30184	23⅝	8¾	4	600	213	102	22⅞	7⅞	4	562	181	102	6	25	8	40150
30174	23⅝	11⅛	4	600	283	102	22⅞	10	4	562	254	102	6	35	16	40170


One color per carton. Specify color: Red, Yellow, or Blue.

Optional Accessories:




Dividers

Black polypropylene dividers create compartments. Sizes to fit all bins except 30110. Each bin accepts up to 7 compartment dividers.



Extended Label Holders

Designed for larger bar code scanning. Label holders fit all shelf bins except the 30110.



Bin Cups

Bin Cups lift out easily for parts retrieval and fit all Shelf Bins. (Refer to Shelf Bin chart for number of cups per bin.)

Dividers

Model No.	Fits Shelf Bins	Width	Pkg. Qty.
40120	30120, 30124, 30128	4 ¹ / ₈ "	24
40130	30130, 30138, 30164	6 ⁵ / ₈ "	24
40150	30150, 30158, 30184	8 ³ / ₈ "	24
40170	30170, 30174, 30178	11 ¹ / ₈ "	24

Extended Label Holders

Model No.	Description	Dimensions W	H	Pkg. Qty.
40410	10° Angle	4"	2 ¹ / ₄ "	24
40445	45° Angle	4"	2 ¹ / ₄ "	24

Bin Cups

Model No.	Description	Dimensions L	W	H	Ctn. Qty.
30101	Small Bin Cup	3 ¹ / ₄ "	2"	3"	48
30102	Large Bin Cup	5"	2 ³ / ₄ "	3"	24

Economy Bins




A large bar code label area make content identification simple.

- The only small parts bin that can nest and stack.
- Help organize work areas and expand storage space without adding shelving.
- Versatile Economy Bins make full use of shelf depth on 12" or 18" deep shelving and stack to fill space between shelves.
- Sturdy one-piece construction is water, rust, and corrosion-proof.
- Unaffected by weak acids and alkalis.
- Molded from co-polymer polypropylene.
- Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty.
- Autoclavable up to 250° F
- Available in 5 sizes.

Unique post & rib design allows the bins to stack and nest

Tapered corners keep small parts from becoming trapped

Stacking posts allow same-width stacking



Reinforced side ribs add strength and prevent spreading

Large label area accommodates long bar codes

Generous opening allows easy access to stored items



30796 Black



30716 Black



30776 Black




30718 Black



30778 Black

Economy Bins


Model No.	Outside Dimensions						Ctn. Qty.
	Inches			mm			
	L	W	H	L	W	H	
30796 Black	8½	6½	5	225	168	127	10 each
30716 Black	11½	6½	5	302	168	127	10 each
30776 Black	17½	6½	7	454	168	178	10 each
30718 Black	11½	8½	5	302	213	127	8 each
30778 Black	17½	8½	7	454	213	178	8 each




1800 Series AkroBins®



30358



- Storage systems for large, heavy, and bulky items.
- Concentrate storage, reduce and control inventories, minimize material handling, and organize supplies.
- Strong, durable co-polymer polypropylene construction.
- Designed to fit on 18" shelving for concentrated storage.
- One black cross-wise divider included per bin.
- Available in 2 sizes: 8 $\frac{1}{4}$ " and 11" width.
- Color: Beige.



1800 Series AkroBins

Outside Dimensions							Inside Dimensions								Ctn. Qty.	Dividers Model No.	Pkg. Qty.	Capacity Lbs.
Model No.	Inches			mm			Inches				mm							
	L	W	H	L	W	H	L	W	H	X	L	W	H	X				
30348	20½	8¼	7	521	210	178	20	7¾	6½	20	508	187	165	508	6	40348	6	60
30358	20½	11	7	521	279	178	20	10⅛	6½	20	508	257	165	508	6	40358	6	75

Order in carton quantities.

ESD Containers

AkroBins®

- Akro-Mils ESD containers dissipate electrostatic charges which can severely damage sensitive electronic components.
- Sturdy, one-piece construction is water, rust, and corrosion proof, and heat resistant to 300°F.



Hanging Systems

- Storage systems provide convenient parts storage and retrieval.
- Six options let you choose the system that works best for you.



Shelf Bins

- Shelf Bins provide an economical solution to electronic component storage problems.
- Works with 12", 18", and 24" deep shelving or vertical storage and retrieval units.



Grids

- Grids are compatible with most racks, shelving, and automated material handling equipment.
- Ribbed design gives added strength.



ESD AkroBins (Black Only)

Model No.	Outside Dimensions						Inside Dimensions								Bin Load Capacity On Rack	Ctn Qty.
	Inches			mm			Inches				mm					
	L	W	H	L	W	H	L	W	H	X	L	W	H	X		
30210ESD	5¾	4⅛	3	136	105	76	4¾	3⅞	2⅜	4	121	87	71	102	10 lbs.	24
30220ESD	7¾	4⅛	3	187	105	76	6¾	3⅞	2⅜	6	171	87	71	152	10 lbs.	24
30230ESD	10⅞	5½	5	276	140	127	10¼	4¾	4¾	9	260	111	121	229	30 lbs.	12
30235ESD	10⅞	11	5	276	279	127	10¼	10	4¾	9	260	254	121	229	50 lbs.	6
30240ESD	14¾	8¼	7	375	210	178	14	6⅞	6¾	12	356	167	171	305	60 lbs.	12

Louvered Panels And Bench Racks

Use this chart to determine the quantity of same-size AkroBins required to fill each panel.

See pages 5-6 for hanging system features.

Model No.	Description	Ctn. Qty.	AkroBin Model No. (Bin Wt. Capacity)				
			30210ESD (10 lbs.)	30220ESD (10 lbs.)	30230ESD (30 lbs.)	30235ESD (50 lbs.)	30240ESD (60 lbs.)
30618	18" x 19" Louvered Panel	4	16	16	9	—	—
30636	35 $\frac{3}{4}$ " x 19" Louvered Panel	4	32	32	18	9	8
98600	27 $\frac{3}{4}$ " Bench Rack	1	30	30	12	6	6
98636	36" Bench Rack	1	40	40	18	9	8

Louvered Floor Racks

Use this chart to determine the quantity of same-size AkroBins required to fill each floor rack.

Bins sold separately.


Model No.	Description	Dimensions						AkroBin Model Number				
		Inches			mm			30210ESD	30220ESD	30230ESD	30235ESD	30240ESD
		L	W	H	L	W	H					
30626	Double-Sided Snap Fastener Louvered Rack	36	20	60	914	508	1524	192	192	108	54	48
30653	Louvered Floor Rack	35 $\frac{3}{4}$	32	75 $\frac{1}{8}$	908	813	1908	288	288	144	72	72

ESD Shelf Bins

Model No.	Outside Dimension						Inside Dimension						Ctn Qty.
	Inches			mm			Inches			mm			
	L	W	H	L	W	H	L	W	H	L	W	H	
30120ESD	11½	4½	4	295	105	102	10¼	3	4	260	76	102	24
30128ESD	17½	4½	4	454	105	102	16½	3	4	419	76	102	12
30124ESD	23¾	4½	4	600	105	102	22½	3	4	562	76	102	12

ESD Grids

Model No.	Outside Dimensions						Inside Dimensions												Ctn. Qty.
	Inches			mm			Inches					mm							
	L	W	H	L	W	H	A	B	C	D	E	A	B	C	D	E			
33164ESD	16½	10⅞	4	419	276	102	9⅜	14⅕	14⅓	9⅓	3⅞	238	379	376	233	98	12		
33224ESD	22⅜	17⅜	4	568	441	102	15⅓	20⅓	20	15	3⅞	383	510	508	381	98	6		



Grounding wire
98100 – Conducts static charges away from the storage system. Designed to convert existing Akro-Mils racks and hanging systems (see pages 5-6).

