



UNIT: mm




CABLE WHITE PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+24AWG/2C
E189529 **PL** AWM STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 20Mohm(min)
4. dielectric test: DC 300V



CNC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWN	Andy	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1010-BL-00500
DECIDED		DATE	2013-8-23
VERSIONS/EDITION	A/0	PROJECTION	
SPECIFICATION			
①	CONN	1set	USB2.0 A MALE SHELL: NICKEL, PIN G/F 3PCS-TYPE INSULATOR COLOR: WHITE
②	CONN	1	USB2.0 A FEMALE SHELL: NICKEL, PIN G/F SHORT TYPE INSULATOR COLOR: WHITE
③	CABLE	1	BLACK USB2.0 UI2725 28#/1P+24#/2C+AEB OD: 4.7mm L=5000±20mm
④	OUT JACKET	6g	BLACK PVC-45P (MOULD NO.: WM-40)
⑤	OUT JACKET	7g	BLACK PVC-45P (MOULD NO.: WM-83)
⑥	IN JACKET	3g	CLEAR LDPE (MOULD NO.: NM-027)
⑦	TIE	1	BLACK L=120mm
⑧	PE BAG	1	CLEAR SIZE: 150*280*0.05mm PRINT BLACK "MADE IN CHINA" 及印生产周期, 有透气孔.
⑨	PE BAG	1/5	CLEAR SIZE: 360*380*0.05mm PRINT BLACK "MADE IN CHINA" + "5PCS" 及印生产周期, 有透气孔.