



HONEYWELL
PART NUMBER


5



NOTE -

- 1 FURNISHED UNASSEMBLED
2 TERMINATION WILL ACCEPT CRIMP CONTACT
CONFORMING TO MIL-39029/1-20 ONLY
3 MATTE FINISH
4 GOLD PLATED CONTACTS
5 SEE CHART FOR CATALOG LISTING

REV	DOCUMENT	CHANGED BY	CHECK
8	0020219	SK 27MAR06	AS



CATALOG LISTING 5	CIRCUIT WITH TOGGLE IN		
	ONE EXTREME POSITION (KEYWAY) 2-1 5-4	CENTER POSITION	OTHER EXTREME POSITION (OPPOSITE KEYWAY) 2-3 5-6
112TW8-1	ON	OFF	ON
112TW8-3	ON	NONE	ON
112TW8-7	MOM ON	OFF	MOM ON
112TW8-8	MOM ON	NONE	ON

CHARACTERISTICS

ELECTRICAL DATA

CONTACT ARRANGEMENT

28 VDC & 125 VAC
.1 AMP RES
.1 AMP IND
.1 AMP LAMP

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:

NO PLACE	X	±	
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	
ANGLES		±	

THIRD ANGLE PROJECTION



DRAWN	KRB	09SEP05
CHECK	RJ	09SEP05

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

RASTER

Honeywell

TITLE

SWITCH - TOGGLE

SIZE	TYPE	DRAWING NAME	REV
B	I	112 TW8 SERIES CHART 1	8
SCALE 2:1		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[112TW8-3](#) [112TW8-7](#)