



Made in Germany

Toll Free: (800) 494-6104

Click image to view web page

Wiha SYSTEM 4 Precision Blades


269 SYSTEM 4 Metric Ball End & Standard Hex, Reversible Blade CVM steel, hardened, chrome-plated, Wiha vapor Chrome-Top finish on tips. One side hex, other side ballpoint hex.

Item					
No.	Size	Size	mm	Inch	lbs.
269 32	1.3 + 1.3	120	4.7	.05	
269 33	1.5 + 1.5	120	4.7	.06	
269 34	2.0 + 2.0	120	4.7	.06	
269 35	2.5 + 2.5	120	4.7	.06	
269 36	3.0 + 3.0	120	4.7	.06	
269 37	4.0 + 4.0	120	4.7	.06	



280 SYSTEM 4 Metric Ball End Hex Interchangeable Blade High alloy tool steel, hardened, corrosion protected. Ballpoint end works at 30° angle entry for easy access to fasteners.

Item					
No.	Size	mm	Inch	lbs.	pkg.
280 33	1.5	120	4.7	.05	1
280 34	2.0	120	4.7	.05	1
280 35	2.5	120	4.7	.06	1
280 36	3.0	120	4.7	.06	1
280 37	4.0	120	4.7	.06	1



280 SYSTEM 4 Inch Ball End Hex Interchangeable Blade High alloy tool steel, hardened, corrosion protected. Ballpoint end works at 30° angle entry for easy access to fasteners.

Item				
No.	Size	mm	Inch	lbs.
280 21	.050	120	4.7	.06
280 23	1/16	120	4.7	.06
280 24	5/64	120	4.7	.06
280 25	3/32	120	4.7	.06
280 26	7/64	120	4.7	.06
280 27	1/8	120	4.7	.06
280 28	9/64	120	4.7	.06
280 29	5/32	120	4.7	.06



269 SYSTEM 4 Metric Hex Sizes, Interchangeable Blade High alloy CVM steel, hardened, corrosion protected.

Item				
No.	Size	mm	Inch	lbs.
269 13	0.7	120	4.7	.06
269 14	0.9	120	4.7	.06
269 15	1.3	120	4.7	.06
269 16	1.5	120	4.7	.06
269 17	2.0	120	4.7	.06
269 18	2.5	120	4.7	.06
269 19	3.0	120	4.7	.06
269 20	4.0	120	4.7	.06



269 SYSTEM 4 Inch Hex Sizes, Interchangeable Blade High alloy chrome-vanadium-molybdenum steel, hardened, corrosion protected.

Item					Each
No.	Size	mm	Inch	lbs.	
269 21	.050	120	4.7	.06	
269 23	1/16	120	4.7	.06	
269 24	5/64	120	4.7	.06	
269 25	3/32	120	4.7	.06	
269 26	7/64	120	4.7	.06	
269 27	1/8	120	4.7	.06	
269 28	9/64	120	4.7	.06	
269 29	5/32	120	4.7	.06	



269 SYSTEM 4 Nut Driver Metric, Interchangeable Blade High alloy chrome-vanadium-molybdenum steel, hardened, corrosion protected. 120mm/4.7" OAL

Item				
No.	Size	Size	Inch	lbs.
269 40	1.5 + 1.8	.12	.12	.03
269 41	2.0 + 2.5	.16	.16	.03
269 38	1.5 -	.11	.11	.04
269 39	1.8 -	.12	.12	.04
269 49	2.0 -	.13	.13	.04
269 50	2.5 -	.16	.16	.04
269 42	3.0 -	.20	.20	.04
269 43	3.2 -	.20	.20	.04
269 44	3.5 -	.22	.24	.04
269 45	4.0 -	.22	.24	.04
269 46	4.5 -	.25	.28	.05
269 47	5.0 -	.27	.28	.05
269 48	5.5 -	.30	.32	.05



269 SYSTEM 4 Nut Driver Inch, Interchangeable Blade. High alloy chrome-vanadium-molybdenum steel, hardened, corrosion protected. 120mm/4.7" OAL

Item				
No.	Size	Inch	Inch	lbs.
269 62	3/32	.16	.16	.04
269 63	7/64	.20	.20	.04
269 64	1/8	.20	.20	.04
269 65	9/64	.21	.24	.04
269 66	5/32	.22	.24	.04
269 67	3/16	.26	.28	.04
269 68	7/32	.30	.32	.04
269 69	1/4	1.34	.36	.04



269 SYSTEM 4 TORX® Reversible Blade High alloy chrome-vanadium-molybdenum steel, hardened, vapor chrome protected, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL.

Item			
No.	Size	Size	lbs.
269 51	T6 + T8		.03
269 52	T7 + T9		.03
269 53	T10 + T15		.03
269 54	T15 + T20		.03



269 SYSTEM 4 TORX® Interchangeable Blade High alloy CVM steel, hardened, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL

Item		
No.	Size	lbs.
269 55	T3	.03
269 56	T4	.03
269 57	T5	.03