

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0508913003](#)
Status: **Obsolete**
Description: Spade Tongue Terminal for 12 AWG, Closed Insulated Vinyl Straight Barrel, Yellow, Stud Size 8 (M4), Oxygen-Free Copper, Length 24.50mm (.965")

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR95446
UL	E134962

General

Product Family	Ring and Spade Terminals
Series	50891
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	VSY (Spade Vinyl Straight)
Type	Spade

Physical

Barrel Type	Closed - Brazed
Color - Resin	Yellow
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	8 (M4)
Wire Size AWG	12
Wire Size mm ²	2.63 - 4.60

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-50891-002
---------------	--------------



Series

image - Reference only

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[50891Series](#)