


(2,54 mm) .100"



BBS, BBL, BHS, BBD, BDL SERIES

MACHINED BOARD STACKING STRIPS

Mates with:
SS, SD, HSS, SL, SDL,
ESS, ESD

FEATURES

- Low profile design achieves (3,89 mm) .153" board spacings when mated with SL Series.
- Approach the reliability of a permanent connection with the flexibility of a separable connection.

SPECIFICATIONS

For complete specifications see www.samtec.com?BBS, www.samtec.com?BBL, www.samtec.com?BHS, www.samtec.com?BBD or www.samtec.com?BDL

Insulator Material:

Black Glass Filled Polyester (BBS, BBD, BBL)

Black High Temp Nylon (BDL)

Black Liquid Crystal Polymer (BHS)

Temperature Range:
-55°C to +125°C

Terminal Material:
Phosphor Bronze or Brass

Plating:

Au or Sn over 50µ" (1,27 µm) Ni

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only (BBS, BBD, BBL, BDL))


Wave, or reflow with all Au (BHS)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note: Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM