




| Best.-Nr. | WIRE RANGE<br>mm <sup>2</sup> / AWG | DIMENSION   |          |        |        |        |        |         | COLOR  |
|-----------|-------------------------------------|-------------|----------|--------|--------|--------|--------|---------|--------|
|           |                                     | STUD SIZE   | d2ø (mm) | B (mm) | L (mm) | F (mm) | H (mm) | Dø (mm) |        |
| 74 55 01  | 0.5~1.5mm <sup>2</sup><br>22~16 AWG | M3 (3.2mm)  | 3.2      | 5.7    | 17.8   | 4.95   | 10     | 4.2     | RED    |
| 74 60 36  |                                     | M3.5(3.7mm) | 3.7      | 5.7    | 18.1   | 6.3    |        |         |        |
| 74 60 48  |                                     | M4 (4.3mm)  | 4.2      | 6.6    | 20.1   | 5.7    |        |         |        |
| 74 60 61  |                                     | M5(5.3mm)   | 5.2      | 8      | 21.5   | 6.7    |        |         |        |
| 74 60 74  |                                     | M6(6.5mm)   | 6.4      | 11.6   | 27.5   | 10.5   |        |         |        |
| 74 67 62  |                                     | M8(8.4mm)   | 8.4      | 11.6   | 27.5   | 11.1   |        |         |        |
| 74 60 87  | 1.5~2.5mm <sup>2</sup><br>16~14 AMG | M3 (3.2mm)  | 3.2      | 6.6    | 18.6   | 4.3    | 10     | 4.7     | BLUE   |
| 74 64 27  |                                     | M3.5(3.7mm) | 3.7      | 6.6    | 17.8   | 4.3    |        |         |        |
| 74 65 42  |                                     | M4 (4.3mm)  | 4.2      | 6.6    | 21     | 6.4    |        |         |        |
| 74 65 55  |                                     | M5(5.3mm)   | 5.2      | 8.5    | 22.5   | 7      |        |         |        |
| 74 65 68  |                                     | M6(6.5mm)   | 6.4      | 12     | 27.6   | 10.5   |        |         |        |
| 74 65 81  |                                     | M8(8.4mm)   | 8.4      | 12     | 27.6   | 11     |        |         |        |
| 74 65 94  | 4~6mm <sup>2</sup><br>12~10 AWG     | M3.5(3.7mm) | 3.7      | 7.2    | 22.7   | 5.9    | 13.5   | 6       | YELLOW |
| 74 66 28  |                                     | M4 (4.3mm)  | 4.3      | 7.2    | 22.8   | 5.9    |        |         |        |
| 74 66 21  |                                     | M5(5.3mm)   | 5.3      | 9.5    | 26.3   | 7.7    |        |         |        |
| 74 66 82  |                                     | M6(6.5mm)   | 6.4      | 12     | 29     | 9.2    |        |         |        |
| 74 67 50  |                                     | M8(8.4mm)   | 8.4      | 15     | 34.5   | 13.7   |        |         |        |

Ring Connector Series