





MODEL	Output Voltage	Output Current (85 ~ 264 VAC)	Efficiency (%)	Ripple & Noise (mVp-p)
KRS10F-05S	5VDC	2.00A	74%	150mVp-p
KRS10F-12S	12VDC	0.84A	79%	150mVp-p
KRS10F-15S	15VDC	0.65A	81%	150mVp-p
KRS10F-24S	24VDC	0.42A	82%	200mVp-p



Note:

- Measurements in millimeter (mm) unless otherwise specified
- Tolerance $\pm 1\text{mm}$

NOTE:

All specifications typical and nominal / full load and 25°C unless otherwise noted.
 Avoid sustained operation in overload or dead short conditions.
 Specifications subject to changes without notice.