





MATL MOLDED ZYTEL 101 NC-10 NATURAL
FINISH NONE

B DWG No. 040-0000-001

INSERTS WITH CA-E
16 & 12 CONTACTS
20 & 16 & 12 CONTACTS
INSERTS WITH CA-E
24 & 4 CONTACTS

CHG.	D.C.R.	REVISIONS	BY	DATE	CHK.
A	-	REDRAWN FOR CLARITY	H	8-15-59	LJS
B	-	"PART NO" COLUMN ADDED	H	11-20-59	LJS
C	-	TITLE WAS "CUP, CA3108ER&AR 10-24"	W	11-24-59	RM
D	RC	ADDED KPT. SIZES 10 THRU 24 & TITLE	E	12-18-59	LJS
E	R/C	MATL. WAS ZYTEL 101 NC-10 NATURAL	W	1-25-60	K
F		REVISED PER DCN M005529	KN	11-15-61	LJS

KPT SIZE	ER&AR SIZE	A ±.020	A ±.020	B ±.005	C ±.020	D ±.005	E ±.010	PART NO
10	10SL	.625	—	1.000	.272	.617	.616	040-0054-000
12	12S-12	.812	—	1.000	.272	.778	.772	-0095
14	14S-14	.812	—	1.000	.303	.852	.850	-0057
—	—	—	1.500	—	—	—	—	-0090
16	16S-16	.812	—	1.250	.375	.984	.975	-0039
—	—	—	1.750	—	—	—	—	-0092
18	18	1.000	—	1.250	.550	1.116	1.110	-0060
—	—	—	1.750	—	—	—	—	-0094
20	20	1.000	—	1.500	.582	1.245	1.235	-0061
—	—	—	1.750	—	—	—	—	-0095
22	22	1.000	—	1.500	.582	1.357	1.360	-0062
—	—	—	1.750	—	—	—	—	-0096
24	24	1.187	—	1.750	.630	1.490	1.485	-0063
—	—	—	1.875	—	—	—	—	-0097
—	—	1.375	—	2.000	.825	1.735	1.735	-0064
—	—	—	1.875	—	—	—	—	-0098
—	—	1.375	—	2.250	.825	2.021	2.021	-0065
—	—	—	1.875	—	—	—	—	-0099
—	—	1.375	—	2.500	.825	2.240	2.240	-0066
—	—	—	1.875	—	—	—	—	040-0100-000

Unless otherwise specified
all dimensions are in inches.
TOLERANCES
Fractional dimensions ± .010
Decimal dimensions ± .002
Angular tolerances ± 1/2°
Remove all burrs and sharp edges

DWN. W.D.H. 8-12-59 CHK. LJS 8-17-59

REF HUGHES

CODE 05081

CUSTOMER DRAWING
CUPPOTTING KPT 08P 10-24
CUPPOTTING, CA3108ER&AR 10SL-36

CANNON ELECTRIC COMPANY
666 East Dyer Road Santa Ana, California
This document and drawings, sketches and
schematic plans are the property of Cannon
Electric Co., and no parts thereof may be
reproduced and used without the written
consent of the owner.

DWG. No. 040-0000-001

CHG. F