



Headers

to Type 169

Type 182 page 120

 Type 183 page 118

to Type 339

Type 188 page 121

 Type 189 page 119

 Type 342 page 120

 Type 343 page 118

Accessories

for Type 169

Coding set

720243 page 205

Type 169

Screw type terminal block, pluggable, centerline 3.5 mm / 0.138 inches, wire entry parallel to plug direction, contact system with integrated wire protection

Technical Data

V / A / AWG 250 / 10 / 28 - 16

V / A / AWG 250 / 10 / 26 - 18

 0.08 - 1 mm² 125 V / 2.5 kV / 5 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 2 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 160 400 400

Rated test voltage 2.5 4 2.5

Protection category according

to IEC 529 IP20

Tightening torque UL 1.3 lb-in max.


Min. insul. strip length 5 mm

Pole size 2 - 18

Color black

Dimensions in mm

1 mm = 0.0394 in.


 $L = (\text{pole size} - 1) \times \text{centerline} + 3.7 \text{ mm} / 0.146 \text{ inches}$

Part numbers (P/N)

(information: page 56)

Complete the part number by adding the pole size.

Type 169

centerline 3.5 mm / 0.138 inches

P/N 311691

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18						

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.

Type 339

Screw type terminal block, pluggable, centerline 3.5 mm / 0.138 inches, wire entry parallel to plug direction, lift system, contact system with integrated wire protection

Technical Data

V / A / AWG 300 / 8 / 28 - 16

 0.08 - 1.5 mm² 130 V / 2.5 kV / 12 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 2.2 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 160 400 400

Rated test voltage 2.5 4 2.5

Protection category according

to IEC 529 IP20

Tightening torque UL 2.2 lb-in max.


Min. insul. strip length 6 mm

Pole size 2 - 12

Color black

Dimensions in mm

1 mm = 0.0394 in.


 $L = (\text{pole size} - 1) \times \text{centerline} + 3.5 \text{ mm} / 0.138 \text{ inches}$

Part numbers (P/N)

(information: page 56)

Complete the part number by adding the pole size.

Type 339

centerline 3.5 mm / 0.138 inches

P/N 313391

	02	03	04	05	06	07	08
09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.