

SECP11GA -- Cord Connectors



Hubbell's nylon cord connectors resist most common industrial corrosive and provide effective pullout protection in a lightweight design. They are ideal for any application where weight, conductivity or corrosion may be an issue.

Product Specifications	
Product Type	Cord Connectors
Material/Style	Nylon Low Profile
Cord Diameter Range	.23"- .40" (5.8-10.0)
Cord Connector Body Style	Straight Male
HUB Size	PG11
Color	 Gray
Material	Polyamide
Sealing Grommet Material	Neoprene
Operating Temperature	-30°C to 100°C
Protection Class	IP68
Flammability	UL 94 V-0
Dimension A	1.181" (30)
Dimension B	.709" (18)
Dimension C	.315 (8)
Dimension D	.40" (10.16)
Dimension E	.984" (25)
Dimension F	.866" (22)
Dimension G	.732" (18.6)
Certifications	UL 514B, CSA C22.2 No. 18
UPC Number	78358501827
Weight in LBs	0.15
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

