


PART NUMBER	SIZE	WIRE RANGE	SEALING RANGE		A ±.010	B ±.010	C MIN	INSERT AND EXTRACT TOOL NUMBER	CRIMP TOOL
			MIN. O.D.	MAX. O.D.					
100060-56	22	26-24-22	.033	.054	.058	.321	.146	M15570-22-1	MH800 WITH POSITIONER K127
1841-1-5616	16	20-18-16	.068	.103	.132	.378	.250	M15570-16	M22520/1-01
1841-1-5612	12	14-12	.106	.158	.188	.418	.250	M15570-12	M22520/1-01
1841-5-5608	8	8	.127	.203	.252	.465	.300	M15515-103	20399

E


D1

D2

SIZE	APPROX. WT. PER CONTACT IN LBS.
22	.0002
16	.0008
12	.0018
8	.0031



SIZE: 16,12,8



SIZE: 22 ONLY

4. FINISH - GOLD PLATE PER MIL-G-45204 TYPE II, CLASS 1.
3. CONTACT MATERIAL - COPPER ALLOY
2. SEE "GENERAL DESCRIPTION" FOR ELECTRICAL AND MATERIAL SPECIFICATION
1. WIRE INSPECTION HOLE (ONE WALL ONLY)
- NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

3.

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±.

1 PLC ±0.1

2 PLC ±0.01

3 PLC ±0.002

4 PLC ±0.0005

ANGLES ±

FINISH

4.

DWN J.P. 681025

CHK B.L. 681122

APVD AR 131028

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

Customer Drawing

TE Connectivity

NAME

CONTACTS, TERMINAL JUNCTION
SIZE: 22,16,12, AND 8
ENVELOPE

SIZE

A3

CAGE CODE

-

DRAWING NO

©61800_DEUTSCH

RESTRICTED TO

-

SCALE

9:1

SHEET

1

OF

1

REV

E