


Type: **A-PKZ0(24VDC)**
Article No.: **073200**




Ordering information

Connection technique		Screw terminals
For use with		PKZM0 PKZM4 PKZM0-T PKM0 PKZM01

Contact sequence



Notes concerning the product group



Accessories

1 Motor-protective circuit-breaker

2 Compact starters, (high-capacity) compact starters

Page

General

Terminal capacities			
Solid or flexible conductor with ferrule		mm ²	1 × (0.75 – 2.5) 2 × (0.75 – 2.5)
Solid or stranded		AWG	1 × (18 – 14) 2 × (18 – 14)

Main conducting paths

Rated operating voltage	U_e	V AC	42 – 480
Rated operating voltage	U_e	V DC	24 – 250

Operating range


AC		× U_s	0,7 – 1,1
DC		× U_s	0,7 – 1,1

Power consumption

AC			
Pick-up AC	Pick-up	VA	5
Sealing AC	Sealing	VA	3
DC			

Pull-in DC	Pick-up	W	3
Sealing DC	Sealing	W	3
Dimensions			

Dimensions



Moeller GmbH, Hein-Moeller-Str. 7-11, D-53115 Bonn
 E-Mail: catalog@moeller.net, Internet: www.moeller.net, <http://catalog.moeller.net>
 Copyright 2005 by Moeller GmbH. Subject to modifications. HPL-C2005GB-INT V3.0