




13			12		11		10		9		8		7		6		5		4		3		2		1			
PACKAGING SEE NOTE 4 SHT 1			4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A				BULK		BULK	
			8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS				TUBES		TUBES	
			DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)				8.13 (.320)					
			PLATING				150 TIN				15 GOLD				30 GOLD				15 GOLD				30 GOLD					
			DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)				4.57 (.180)					
CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS	
	MM	IN	MM	IN																								
04	5.08	.200	2.54	.100	015-91-2040	015-91-6040	N/A	015-91-0040	015-91-6042	N/A	015-91-3040	015-91-6043	N/A		015-91-0048	015-91-5049	04											
06	7.62	.300	5.08	.200	015-91-2060	015-91-6060	N/A	015-91-0060	015-91-6062	N/A	015-91-3060	015-91-6063	N/A		015-91-0068	015-91-5069	06											
08	10.16	.400	7.62	.300	015-91-2080	015-91-6080	015-91-3087	015-91-0080	015-91-6082	015-91-3086	015-91-3080	015-91-6083	015-91-3088		015-91-0088	015-91-5089	08											
10	12.70	.500	10.16	.400	015-91-2100	015-91-6100	015-91-3107	015-91-0100	015-91-6102	015-91-3106	015-91-3100	015-91-6103	015-91-3108		015-91-0108	015-91-5109	10											
12	15.24	.600	12.70	.500	015-91-2120	015-91-6120	015-91-3127	015-91-0120	015-91-6122	015-91-3126	015-91-3120	015-91-6123	015-91-3128		015-91-0128	015-91-5129	12											
14	17.78	.700	15.24	.600	015-91-2140	015-91-6140	015-91-3147	015-91-0140	015-91-6142	015-91-3146	015-91-3140	015-91-6143	015-91-3148		015-91-0148	015-91-5149	14											
16	20.32	.800	17.78	.700	015-91-2160	015-91-6160	015-91-3167	015-91-0160	015-91-6162	015-91-3166	015-91-3160	015-91-6163	015-91-3168		015-91-0168	015-91-5169	16											
18	22.86	.900	20.32	.800	015-91-2180		015-91-3187	015-91-0180		015-91-3186	015-91-3180		015-91-3188		015-91-0188	015-91-5189	18											
20	25.40	1.000	22.86	.900	015-91-2200	015-91-6200	015-91-3207	015-91-0200	015-91-6202	015-91-3206	015-91-3200	015-91-6203	015-91-3208		015-91-0208	015-91-5209	20											
22	27.94	1.100	25.40	1.000	015-91-2220		015-91-3227	015-91-0220		015-91-3226	015-91-3220		015-91-3228		015-91-0228	015-91-5229	22											
24	30.48	1.200	27.94	1.100	015-91-2240		015-91-3247	015-91-0240		015-91-3246	015-91-3240		015-91-3248		015-91-0248	015-91-5249	24											
26	33.02	1.300	30.48	1.200	015-91-2260	015-91-6260	015-91-3267	015-91-0260	015-91-6262	015-91-3266	015-91-3260		015-91-3268		015-91-0268	015-91-5269	26											
28	35.56	1.400	33.02	1.300	015-91-2280		015-91-3287	015-91-0280		015-91-3286	015-91-3280		015-91-3288		015-91-0288	015-91-5289	28											
30	38.10	1.500	35.56	1.400	015-91-2300		015-91-3307	015-91-0300		015-91-3306	015-91-3300		015-91-3308		015-91-0308	015-91-5309	30											
32	40.64	1.600	38.10	1.500	015-91-2320		015-91-3327	015-91-0320		015-91-3326	015-91-3320		015-91-3328		015-91-0328	015-91-5329	32											
34	43.18	1.700	40.64	1.600	015-91-2340		015-91-3347	015-91-0340		015-91-3346	015-91-3340		015-91-3348		015-91-0348	015-91-5349	34											
36	45.72	1.800	43.18	1.700	015-91-2360		015-91-3367	015-91-0360		015-91-3366	015-91-3360		015-91-3368		015-91-0368	015-91-5369	36											
38	48.26	1.900	45.72	1.800	015-91-2380		015-91-3387	015-91-0380		015-91-3386	015-91-3380		015-91-3388		015-91-0388	015-91-5389	38											
40	50.80	2.000	48.26	1.900	015-91-2400	015-91-6400	015-91-3407	015-91-0400	015-91-6402	015-91-3406	015-91-3400	015-91-6403	015-91-3408		015-91-0408	015-91-5409	40											
42	53.34	2.100	50.80	2.000	015-91-2420		015-91-3427	015-91-0420		015-91-3426	015-91-3420		015-91-3428		015-91-0428	015-91-5429	42											
44	55.88	2.200	53.34	2.100	015-91-2440		015-91-3447	015-91-0440		015-91-3446	015-91-3440		015-91-3448		015-91-0448	015-91-5449	44											
46	58.42	2.300	55.88	2.200	015-91-2460		015-91-3467	015-91-0460		015-91-3466	015-91-3460		015-91-3468		015-91-0468	015-91-5469	46											
48	60.96	2.400	58.42	2.300	015-91-2480		015-91-3487	015-91-0480		015-91-3486	015-91-3480		015-91-3488		015-91-0488	015-91-5489	48											
50	63.50	2.500	60.96	2.400	015-91-2500	015-91-6500	015-91-3507	015-91-0500	015-91-6502	015-91-3506	015-91-3500	015-91-6503	015-91-3508		015-91-0508	015-91-5509	50											
52	66.04	2.600	63.50	2.500	015-91-2520		015-91-3527	015-91-0520		015-91-3526	015-91-3520		015-91-3528		015-91-0528	015-91-5529	52											
54	68.58	2.700	66.04	2.600	015-91-2540		015-91-3547	015-91-0540		015-91-3546	015-91-3540		015-91-3548		015-91-0548	015-91-5549	54											
56	71.12	2.800	68.58	2.700	015-91-2560		015-91-3567	015-91-0560		015-91-3566	015-91-3560		015-91-3568		015-91-0568	015-91-5569	56											
58	73.66	2.900	71.12	2.800	015-91-2580		015-91-3587	015-91-0580		015-91-3586	015-91-3580		015-91-3588		015-91-0588	015-91-5589	58											
60	76.20	3.000	73.66	2.900	015-91-2600		015-91-3607	015-91-0600		015-91-3606	015-91-3600		015-91-3608		015-91-0608	015-91-5609	60											
62	78.74	3.100	76.20	3.000	015-91-2620		015-91-3627	015-91-0620		015-91-3626	015-91-3620		015-91-3628		015-91-0628	015-91-5629	62											
64	81.28	3.200	78.74	3.100	015-91-2640		015-91-3647	015-91-0640		015-91-3646	015-91-3640		015-91-3648		015-91-0648	015-91-5649	64											
66	83.82	3.300	81.28	3.200	015-91-2660		015-91-3667	015-91-0660		015-91-3666	015-91-3660		015-91-3668		015-91-0668	015-91-5669	66											
68	86.36	3.400	83.82	3.300	015-91-2680		015-91-3687	015-91-0680		015-91-3686	015-91-3680		015-91-3688		015-91-0688	015-91-5689	68											
70	88.90	3.500	86.36	3.400	015-91-2700		015-91-3707	015-91-0700		015-91-3706	015-91-3700		015-91-3708		015-91-0708	015-91-5709	70											
72	91.44	3.600	88.90	3.500	015-91-2720		015-91-3727	015-91-0720		015-91-3726	015-91-3720		015-91-3728		015-91-0728	015-91-5729	72											
74	93.98	3.700	91.44	3.600	015-91-2740		015-91-3747	015-91-0740		015-91-3746	015-91-3740		015-91-3748		015-91-0748	015-91-5749	74											
76	96.52	3.800	93.98	3.700	015-91-2760		015-91-3767	015-91-0760		015-91-3766	015-91-3760		015-91-3768		015-91-0768	015-91-5769	76											
78	99.06	3.900	96.52	3.800	015-91-2780		015-91-3787	015-91-0780		015-91-3786	015-91-3780		015-91-3788		015-91-0788	015-91-5789	78											
80	101.60	4.000	99.06	3.900	015-91-2800		015-91-3807	015-91-0800		015-91-3806	015-91-3800		015-91-3808		015-91-0808	015-91-5809	80											
82	104.14	4.100	101.60	4.000	71308-0082		71308-0482	71308-0182		71308-0582	71308-0282		71308-0682		71308-1182	71308-1282	82											
84	106.68	4.200	104.14	4.100	71308-0084		71308-0484	71308-0184		71308-0584	71308-0284		71308-0684		71308-1184	71308-1284	84											
86	109.22	4.300	106.68	4.200	71308-0086		71308-0486	71308-0186		71308-0586	71308-0286		71308-0686		71308-1186	71308-1286	86											
88	111.76	4.400	109.22	4.300	71308-0088		71308-0488	71308-0188		71308-0588	71308-0288		71308-0688		71308-1188	71308-1288	88											
90	114.30	4.500	111.76	4.400	71308-0090		713																					

13			12		11		10		9		8	7	6	5	4	3	2		1										
			PACKAGING SEE NOTE 4 SHT 1			4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK					
						10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TUBES		TUBES					
						DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)		8.13 (.320)		8.13 (.320)			
						PLATING				150 TIN				15 GOLD				30 GOLD				150 TIN		15 GOLD		30 GOLD			
						DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)		4.57 (.180)		4.57 (.180)			
CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS								
	MM	IN	MM	IN	MM	IN																							
04	5.08	.200	2.54	.100	----	----	015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040						04								
06	7.62	.300	5.08	.200	2.54	.100	015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060						06								
08	10.16	.400	7.62	.300	5.08	.200	015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080						08								
10	12.70	.500	10.16	.400	7.62	.300	015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100						10								
12	15.24	.600	12.70	.500	10.16	.400	015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120						12								
14	17.78	.700	15.24	.600	12.70	.500	015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140						14								
16	20.32	.800	17.78	.700	15.24	.600	015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160						16								
18	22.86	.900	20.32	.800	17.78	.700	015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180						18								
20	25.40	1.000	22.86	.900	20.32	.800	015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200						20								
22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220						22								
24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240						24								
26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260						26								
28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280						28								
30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300						30								
32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320						32								
34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340						34								
36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360						36								
38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380						38								
40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400						40								
42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420						42								
44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440						44								
46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460						46								
48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480						48								
50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500						50								
52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520						52								
54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540						54								
56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560						56								
58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580						58								
60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600						60								
62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620						62								
64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640						64								
66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660						66								
68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680						68								
70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700						70								
72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720						72								
74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740						74								
76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760						76								
78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780						78								
80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800						80								
82	104.14	4.100	101.60	4.000	99.06	3.900	71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282						82								
84	106.68	4.200	104.14	4.100	101.60	4.000	71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284						84								
86	109.22	4.300	106.68	4.200	104.14	4.100	71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286						86								
88	111.76	4.400	109.22	4.300	106.68	4.200	71308-4088		71308-4188		71308-4288		71308-5088	71308-5188	71308-5288						88								
90	114.30	4.500	111.76	4.400	109.22	4.300	71308-4090		71308-4190		71308-4290		71308-5090	71308-5190	71308-5290						90								
92	116.84	4.600	114.30	4.500	111.76	4.400	71308-4092		71308-4192		71308-4292		71308-5092	71308-5192	71308-5292						92								
94	119.38	4.700	116.84	4.600	114.30	4.500	71308-4094		71308-4194		71308-4294		71308-5094	71308-5194	71308-5294						94								
96	121.92	4.800	119.38	4.700	116.84	4.600	71308-4096		71308-4196		71308-4296		71308-5096	71308-5196	71308-5296						96								
98	124.46	4.900	121.92	4.800	119.38	4.700	71308-4098		71308-4198		71308-4298		71308-5098	71308-5198	71308-5298						98								
100	127.00	5.000	124.46	4.900	121.92	4.800	71308-																						

		13		12		11		10		9		8		7		6		5		4		3		2		1				
J			PACKAGING SEE NOTE 4 SHT 1		4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS																	
					10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS																	
					DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)																	
					PLATING				30 GOLD				150 TIN																	
					DIM. H				2.54 (.100)				2.54 (.100)																	
I	CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS		
		MM	IN	MM	IN	MM	IN																							
H	04	5.08	.200	2.54	.100	----	----	015-91-1048	015-91-6047																			04		
	06	7.62	.300	5.08	.200	2.54	.100	015-91-1068	015-91-6067	71308-6106	71308-6206																06			
	08	10.16	.400	7.62	.300	5.08	.200	015-91-1088	015-91-6087	71308-6108	71308-6208															08				
	10	12.70	.500	10.16	.400	7.62	.300	015-91-1108	015-91-6107	71308-6110	71308-6210															10				
	12	15.24	.600	12.70	.500	10.16	.400	015-91-1128																		12				
	14	17.78	.700	15.24	.600	12.70	.500	015-91-1148	015-91-6147																	14				
	16	20.32	.800	17.78	.700	15.24	.600	015-91-1168	015-91-6167																	16				
	18	22.86	.900	20.32	.800	17.78	.700	015-91-1188																		18				
	20	25.40	1.000	22.86	.900	20.32	.800	015-91-1208	015-91-6207																	20				
	22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1228																		22				
G	24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1248																		24				
	26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1268		71308-6126															26					
	28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1288																	28					
	30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1308																	30					
	32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1328																	32					
	34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1348																	34					
	36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1368																	36					
	38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1388																	38					
	40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1408	015-91-6407																40					
	42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1428																	42					
F	44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1448																	44					
	46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1468																	46					
	48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1488																	48					
	50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1508	015-91-6507															50						
	52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1528																	52					
	54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1548																	54					
E	56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1568																	56					
	58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1588																	58					
	60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1608																	60					
	62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1628																	62					
	64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1648																	64					
	66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1668																	66					
	68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1688																	68					
	70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1708																	70					
	72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1728																	72					
	74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1748																	74					
D	76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1768																	76					
	78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1788																	78					
	80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1808																	80					
	82	104.14	4.100	101.60	4.000	99.06	3.900	71308-6082																	82					
	84	106.68	4.200	104.14	4.100	101.60	4.000	71308-6084																	84					
	86	109.22	4.300	106.68	4.200	104.14	4.100	71308-6086																	86					
C	88	111.76	4.400	109.22	4.300	106.68	4.200	71308-6088																	88					
	90	114.30	4.500	111.76	4.400	109.22	4.300	71308-6090																	90					
	92	116.84	4.600	114.30	4.500	111.76	4.400	71308-6092																	92					
	94	119.38	4.700	116.84	4.600	114.30	4.500	71308-6094																	94					
	96	121.92	4.800	119.38	4.700	116.84	4.600	71308-6096																	96					
	98	124.46	4.900	121.92	4.800	119.38	4.700	71308-6098																	98					
	100	127.00	5.000	124.46	4.900	121.92	4.800	71308-6100																	100					
	B	SHORT PEG VERSION (.055")																										B		
	A																											A		
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1						
SEE SHEET 1 EC NO: UCP2014-0809 DRWN:MK/PPER CHKD:JBELL APPR:FSMITH 2013/08/20 2013/08/20 2013/09/03		DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		TITLE SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100 molex		DOCUMENT NO. SD-71308-001		SHEET NO. 5 OF 6												
				DRAWN BY DATE KMS 1999/10/15		CHECKED BY DATE KMS 1999/10/15		APPROVED BY DATE KMS 1999/10/15																						
K5		REV		ANGULAR ±1/2°		SEE TABLE		MATERIAL NO.																						
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						

		13		12		11		10		9		8		7		6		5		4		3		2		1											
J		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/VAC CAPS		N/A		4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		LONG PEG VERSION (.130")		SHORT PEG VERSION (.055")															
						TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS				10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES								BULK		TAPE-N-REEL W/ VAC CAPS					
				8-100 CKT																																	
						DIM. M±0.25 MM				6.10 (.240)								8.13(.320)		13.59(.535)		6.10(.240)								8.13(.320)		6.10 (.240)					
				PLATING				59 TIN								59 TIN		59 TIN		59 TIN		59 TIN								59 TIN							
DIM. H						2.54(.100)								4.57(.180)		4.57(.180)		2.54(.100)		4.57(.180)		2.54(.100)															
I		CKTS		DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS							
				MM IN		MM IN		MM IN		---		---		---		---		---		---		---		---		---		---		---		---					
H		04		5.08 .200		2.54 .100		---		---		71308-5404		71308-5504		N/A				71308-6404		71308-6504		71308-6604		71308-6706		71308-6806		04							
		06		7.62 .300		5.08 .200		2.54 .100		---		71308-5406		71308-5506		N/A				71308-6406		71308-6506		71308-6606		71308-6708		71308-6808		06							
		08		10.16 .400		7.62 .300		5.08 .200		---		71308-5408		71308-5508		71308-5608				71308-6408		71308-6508		71308-6608		71308-6708		71308-6808		08							
		10		12.70 .500		10.16 .400		7.62 .300		---		71308-5410		71308-5510		71308-5610				71308-6410		71308-6510		71308-6610		71308-6710		71308-6810		10							
		12		15.24 .600		12.70 .500		10.16 .400		---		71308-5412		71308-5512		71308-5612				71308-6412		71308-6512		71308-6612						12							
		14		17.78 .700		15.24 .600		12.70 .500		---		71308-5414		71308-5514		71308-5614				71308-6414		71308-6514		71308-6614						14							
		16		20.32 .800		17.78 .700		15.24 .600		---		71308-5416		71308-5516		71308-5616				71308-6416		71308-6516		71308-6616						16							
		18		22.86 .900		20.32 .800		17.78 .700		---		71308-5418				71308-5618				71308-6418				71308-6618						18							
		20		25.40 1.000		22.86 .900		20.32 .800		---		71308-5420		71308-5520		71308-5620				71308-6420				71308-6620						20							
		22		27.94 1.100		25.40 1.000		22.86 .900		---		71308-5422				71308-5622				71308-6422				71308-6622						22							
G		24		30.48 1.200		27.94 1.100		25.40 1.000		---		71308-5424				71308-5624		71308-5724		71308-6424				71308-6624						24							
		26		33.02 1.300		30.48 1.200		27.94 1.100		---		71308-5426				71308-5626				71308-6426				71308-6626		71308-6726				26							
		28		35.56 1.400		33.02 1.300		30.48 1.200		---		71308-5428				71308-5628				71308-6428				71308-6628						28							
		30		38.10 1.500		35.56 1.400		33.02 1.300		---		71308-5430				71308-5630				71308-6430				71308-6630						30							
		32		40.64 1.600		38.10 1.500		35.56 1.400		---		71308-5432				71308-5632				71308-6432				71308-6632						32							
		34		43.18 1.700		40.64 1.600		38.10 1.500		---		71308-5434				71308-5634				71308-6434				71308-6634						34							
		36		45.72 1.800		43.18 1.700		40.64 1.600		---		71308-5436				71308-5636				71308-6436				71308-6636						36							
		38		48.26 1.900		45.72 1.800		43.18 1.700		---		71308-5438				71308-5638				71308-6438				71308-6638						38							
		40		50.80 2.000		48.26 1.900		45.72 1.800		---		71308-5440		71308-5540		71308-5640				71308-6440				71308-6640						40							
		42		53.34 2.100		50.80 2.000		48.26 1.900		---		71308-5442				71308-5642				71308-6442				71308-6642						42							
F		44		55.88 2.200		53.34 2.100		50.80 2.000		---		71308-5444				71308-5644				71308-6444				71308-6644						44							
		46		58.42 2.300		55.88 2.200		53.34 2.100		---		71308-5446				71308-5646				71308-6446				71308-6646						46							
		48		60.96 2.400		58.42 2.300		55.88 2.200		---		71308-5448				71308-5648				71308-6448				71308-6648						48							
		50		63.50 2.500		60.96 2.400		58.42 2.300		---		71308-5450		71308-5550		71308-5650				71308-6450		71308-6550		71308-6650						50							
		52		66.04 2.600		63.50 2.500		60.96 2.400		---		71308-5452				71308-5652				71308-6452				71308-6652						52							
		54		68.58 2.700		66.04 2.600		63.50 2.500		---		71308-5454				71308-5654				71308-6454				71308-6654						54							
		56		71.12 2.800		68.58 2.700		66.04 2.600		---		71308-5456				71308-5656				71308-6456				71308-6656						56							
		58		73.66 2.900		71.12 2.800		68.58 2.700		---		71308-5458				71308-5658				71308-6458				71308-6658						58							
		60		76.20 3.000		73.66 2.900		71.12 2.800		---		71308-5460				71308-5660				71308-6460				71308-6660						60							
		62		78.74 3.100		76.20 3.000		73.66 2.900		---		71308-5462				71308-5662				71308-6462				71308-6662						62							
D		64		81.28 3.200		78.74 3.100		76.20 3.000		---		71308-5464				71308-5664				71308-6464				71308-6664						64							
		66		83.82 3.300		81.28 3.200		78.74 3.100		---		71308-5466				71308-5666				71308-6466				71308-6666						66							
		68		86.36 3.400		83.82 3.300		81.28 3.200		---		71308-5468				71308-5668				71308-6468				71308-6668						68							
		70		88.90 3.500		86.36 3.400		83.82 3.300		---		71308-5470				71308-5670				71308-6470				71308-6670						70							
		72		91.44 3.600		88.90 3.500		86.36 3.400		---		71308-5472				71308-5672				71308-6472				71308-6672						72							
		74		93.98 3.700		91.44 3.600		88.90 3.500		---		71308-5474				71308-5674				71308-6474				71308-6674						74							
		76		96.52 3.800		93.98 3.700		91.44 3.600		---		71308-5476				71308-5676				71308-6476				71308-6676						76							
		78		99.06 3.900		96.52 3.800		93.98 3.700		---		71308-5478				71308-5678				71308-6478				71308-6678						78							
		80		101.60 4.000		99.06 3.900		96.52 3.800		---		71308-5480				71308-5680				71308-6480				71308-6680						80							
		82		104.14 4.100		101.60 4.000		99.06 3.900		---		71308-5482				71308-5682				71308-6482				71308-6682						82							
C		84		106.68 4.200		104.14 4.100		101.60 4.000		---		71308-5484				71308-5684				71308-6484				71308-6684						84							
		86		109.22 4.300		106.68 4.200		104.14 4.100		---		71308-5486				71308-5686				71308-6486				71308-6686						86							
		88		111.76 4.400		109.22 4.300		106.68 4.200		---		71308-5488				71308-5688				71308-6488				71308-6688						88							
		90		114.30 4.500		111.76 4.400		109.22 4.300		---		71308-5490				71308-5690				71308-6490				71308-6690						90							
		92		116.84 4.600		114.30 4.500		111.76 4.400		---		71308-5492				71308-5692				71308-6492				71308-6692						92							
		94		119.38 4.700		116.84 4.600		114.30 4.500		---		71308-5494				71308-5694				71308-6494				71308-6694						94							
		96		121.92 4.800		119.38 4.700		116.84 4.600		---		71308-5496				71308-5696				71308-6496				71308-6696						96							
		98		124.46 4.900		121.92 4.800		119.38 4.700		---		71308-5498				71308-5698				71308-6498				71308-6698						98							
		100		127.00 5.000		124.46 4.900		121.92 4.800		---		71308-5500				71308-5700				71308-6500				71308-6700						100							
		B		59 TIN PLATE ASSEMBLIES		SEE SHEET 1 EC NO: UCP2014-0809 DRWN:MKIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± .010 1 PLACE ± 0.25 ± --- 0 PLACE ± --- ± --- ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE MM/IN DRAWN BY DATE KMS 1999/10/15 CHECKED BY DATE KMS 1999/10/15 APPROVED BY DATE KMS 1999/10/15 MATERIAL NO. SEE TABLE SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SCALE INCH		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100 molex SD-71308-001 6 OF 6																	
A																																					