

Models 72923

SMD Test Probe W/ Sharp, Spring Mounted Tip, 2MM



Features

- **SMD test probe with sharp, spring mounted tip and 2mm jack**
- Provides ultra-fine control for probing high density SMD circuits
- Very fine 0.03in (0.7mm) diameter stainless steel tip is spring-mounted for controlled pressure
- Removable, clear IC insulator cap prevents shorting of adjacent IC logos.
- Sheathed 2mm receptacle adapts to 2mm test leads and adapters.


Materials

- Probe Body: Brass
- Probe Tip: Steel
- Insulation: Polypropylene
- Cap Insulation: Polypropylene

Ordering Information

Model:72923-Color

Available colors: Black (-0), or Red (-2)



Specifications

Max Current	Max. 1A
Max Voltage	600 V Cat III
Temperature	-20° C + 80° C
Max Resistance	Less than 5 mΩ

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ± 0.02 " (.51 mm), .xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.