



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'PLT2S-C71'

Your search criteria matched only one product, shown below

PLT2S-C71



- Designed for harsh environments where a cable tie material is required to hold up to chemical, high radiation, and/or high operating temperature environments
- Non-conductive material that is excellent for high temperature applications up to 500°F (260° C)
- Flammability rating of UL 94V -0 with low smoke and toxicity
- PEEK material meets MIL specification MIL -P-46183, and is approved for use by The Department of Defense

	Part Number	PLT2SC71
	RoHS Compliance Status	Compliant
	Part Description	Cable Tie, Locking, 7.4", Standard cross section
	Product Type	Cable Ties
	Material	Polyetheretherketone (PEEK)
	Color	Translucent Brown
	CSA Certified	No
	UL Listed (File #E56854)	No
	UL Recognized (File #E56854)	No
	Length (In.)	7.4
	Length (mm)	188
	Width (In.)	.190
	Width (mm)	4.8
	CE Compliant	No
	Cross Section	Standard
	Head Height (In.)	.240
	Head Height (mm)	6.1
	Head Width (In.)	.320
	Head Width (mm)	8.1
	Locking Style	Locking
	Material Flammability Rating	UL 94V-0
	Max. Bundle Diameter (In.)	1.88
	Max. Bundle Diameter (mm)	48
	Max. Continuous Use Temperature	500°F (260°C)
	Min. Loop Tensile Strength (Lbs.)	150
	Min. Loop Tensile Strength (N)	668
	Pricing Description	Cable Tie, 7.4"L (188mm), Standard, PEEK, Brown
	Thickness (In.)	.055
	Thickness (mm)	1.4
	Tool	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
	Min. Order UOM	PC
	Min. Order Qty.	100
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.