

SOLID ABS 2819 13 T



Sample photo

Order symbol: ABS 2819 13 T
Product nbr: 5880060
Description: Enclosure, ABS
Remarks: Transparent cover

EAN: 6418074039149
El. number:
Finland: 3423756
Italy: 7410220
Sweden: 2539739
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm: 278	188	130		Ingress Protection (EN 60529): IP 66/67
inch: 10.9	7.4	5.1		Impact Resistance (EN 62262): IK 08
Materials:				Electrical insulation: Totally insulated
Material:	ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:	Clear transparent			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:	Polyamide			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Cover screws colour:	Grey			Certificates:
Gasket material:	Polyurethane			Fimko
Temperatures:				Europe EN 62208: 2003
Short term:	-40 ... 80 °C			Gost R
Continuous:	-40 ... 60 °C			
Short term:	-40 ... 175 °F			
Continuous:	-40 ... 140 °F			
Accessories:				
EKJVT	Mounting plate			
EKJXT	Mounting plate Pertinax			
EKV 12	DIN-35 Mounting rail			
EKV 22	DIN-35 Mounting rail			
EKJZR	Extension frame			

SOLID 278x188x130-180

