

LAMINATED TRANSFORMERS

Type EI38 / 13.6 - 3.2VA




AGENCY APPROVALS 

1. UL 506, File E113449 


3. EN61558 

-  Frequency 50/60Hz
-  Potted under vacuum
-  Split-bobbin
-  Temperature class ta 70°C/B
-  Weight: 0.155kg
-  Packaging unit: 25 pieces (tray)

Mechanical



Schematics



* Empty-Pin

Primary (V)	Secondary (V / mA)	No-Load Voltage (V)	Schematic No.	Part Number	Agency Approvals
230	6 / 534	9.20	1	038-5187.0	1/3*
230	9 / 356	13.95	1	038-5190.0	1/3*
230	12 / 267	17.80	1	038-5193.0	1/3*
230	15 / 214	22.20	1	038-5196.0	1/3*
230	18 / 178	27.00	1	038-5199.0	1/3*
230	24 / 134	35.00	1	038-5205.0	1/3*
230	2x6 / 267	2x8.90	2	038-5210.0	1/3*
230	2x9 / 178	2x13.40	2	038-5213.0	1/3*
230	2x12 / 134	2x17.50	2	038-5216.0	1/3*
230	2x15 / 107	2x22.30	2	038-5219.0	1/3*
230	2x18 / 89	2x25.80	2	038-5222.0	1
230	2x24 / 67	2x35.90	2	038-5228.0	1
115	6 / 534	9.20	1	038-5049.0	1/3*
115	9 / 356	13.95	1	038-5052.0	1/3*
115	12 / 267	17.80	1	038-5055.0	1/3*
115	15 / 214	22.20	1	038-5058.0	1/3*
115	18 / 178	27.00	1	038-5061.0	1/3*
115	24 / 134	35.00	1	038-5067.0	1/3*
115	2x6 / 267	2x8.90	2	038-5072.0	1/3*
115	2x9 / 178	2x13.40	2	038-5075.0	1/3*
115	2x12 / 134	2x17.50	2	038-5078.0	1/3*
115	2x15 / 107	2x22.30	2	038-5081.0	1/3*
115	2x18 / 89	2x25.80	2	038-5084.0	1
115	2x24 / 67	2x35.90	2	038-5090.0	1
2x115	6 / 534	9.20	3	038-5325.0	1/3*
2x115	9 / 356	13.95	3	038-5328.0	1/3*
2x115	12 / 267	17.80	3	038-5331.0	1/3*
2x115	15 / 214	22.20	3	038-5334.0	1/3*
2x115	18 / 178	27.00	3	038-5337.0	1/3*
2x115	24 / 134	35.00	3	038-5343.0	1/3*
2x115	2x6 / 267	2x8.90	4	038-5348.0	1/3*
2x115	2x9 / 178	2x13.40	4	038-5351.0	1/3*
2x115	2x12 / 134	2x17.50	4	038-5354.0	1/3*
2x115	2x15 / 107	2x22.30	4	038-5357.0	1/3*
2x115	2x18 / 89	2x25.80	4	038-5360.0	1
2x115	2x24 / 67	2x35.90	4	038-5366.0	1

*NOTE: When checking the approval status of this product with VDE, add the prefix "BV" and the suffix "F" to the orderable Part Number (these letters will also be found on the part label). The prefix and suffix are not part of the orderable Part Number.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

<u>038-5049-0</u>	<u>038-5052-0</u>	<u>038-5055-0</u>	<u>038-5058-0</u>	<u>038-5061-0</u>	<u>038-5067-0</u>	<u>038-5072-0</u>	<u>038-5075-0</u>	<u>038-5078-0</u>
<u>038-5081-0</u>	<u>038-5084-0</u>	<u>038-5090-0</u>	<u>038-5187-0</u>	<u>038-5190-0</u>	<u>038-5193-0</u>	<u>038-5196-0</u>	<u>038-5199-0</u>	<u>038-5205-0</u>
<u>038-5210-0</u>	<u>038-5213-0</u>	<u>038-5216-0</u>	<u>038-5219-0</u>	<u>038-5222-0</u>	<u>038-5228-0</u>	<u>038-5325-0</u>	<u>038-5328-0</u>	<u>038-5331-0</u>
<u>038-5334-0</u>	<u>038-5337-0</u>	<u>038-5343-0</u>	<u>038-5348-0</u>	<u>038-5351-0</u>	<u>038-5354-0</u>	<u>038-5357-0</u>	<u>038-5360-0</u>	<u>038-5366-0</u>
<u>038-5400-0</u>	<u>038-5401-0</u>	<u>038-5402-0</u>	<u>038-5403-0</u>	<u>038-5404-0</u>	<u>038-5405-0</u>	<u>038-5406-0</u>	<u>038-5407-0</u>	<u>038-5408-0</u>
<u>038-5409-0</u>	<u>038-5410-0</u>	<u>038-5411-0</u>	<u>038-5412-0</u>	<u>038-5413-0</u>	<u>038-5414-0</u>	<u>038-5415-0</u>	<u>038-5416-0</u>	<u>038-5417-0</u>
<u>038-5418-0</u>	<u>038-5419-0</u>	<u>038-5420-0</u>	<u>038-5421-0</u>	<u>038-5422-0</u>	<u>038-5423-0</u>	<u>038-5424-0</u>	<u>038-5425-0</u>	<u>038-5426-0</u>
<u>038-5427-0</u>	<u>038-5428-0</u>	<u>038-5429-0</u>	<u>038-5430-0</u>	<u>038-5431-0</u>	<u>038-5432-0</u>	<u>038-5433-0</u>	<u>038-5434-0</u>	<u>038-5435-0</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

<u>038-5049-0</u>	<u>038-5052-0</u>	<u>038-5055-0</u>	<u>038-5058-0</u>	<u>038-5061-0</u>	<u>038-5067-0</u>	<u>038-5072-0</u>	<u>038-5075-0</u>	<u>038-5078-0</u>
<u>038-5081-0</u>	<u>038-5084-0</u>	<u>038-5090-0</u>	<u>038-5187-0</u>	<u>038-5190-0</u>	<u>038-5193-0</u>	<u>038-5196-0</u>	<u>038-5199-0</u>	<u>038-5205-0</u>
<u>038-5210-0</u>	<u>038-5213-0</u>	<u>038-5216-0</u>	<u>038-5219-0</u>	<u>038-5222-0</u>	<u>038-5228-0</u>	<u>038-5325-0</u>	<u>038-5328-0</u>	<u>038-5331-0</u>
<u>038-5334-0</u>	<u>038-5337-0</u>	<u>038-5343-0</u>	<u>038-5348-0</u>	<u>038-5351-0</u>	<u>038-5354-0</u>	<u>038-5357-0</u>	<u>038-5360-0</u>	<u>038-5366-0</u>