

NTE[®]
ELECTRONICS, INC.

ECG[®]

NEW!

WIRELESS INSPECTION CAMERA

Extend your vision & reach!



WIC-1™

**With Removable
Color LCD Monitor**



**Detachable Monitor
Adds Convenience!**

*Transmission distance = 30 Feet

Extend your vision & reach!

The new ECG Wireless Inspection Camera allows for **easy visual inspections in hard-to-reach areas, even in total darkness or underwater**, with 2 super bright LEDs! Lightweight, **handheld design** helps you easily find, diagnose, and solve problems.

www.WirelessInspectionCamera.com


Applications:

- HVAC Inspection
- Automotive Inspection
- Cable Routing
- Electrical
- General Contracting
- Home Theater Installation
- Plumbing Inspection
- Much more!


Features:

- 2.4" Removable Color LCD Monitor
- Waterproof Camera & Shaft (IP67)
- Video Out for Recording
- Includes Mirror, Hook, & Magnet Tips
- One Year Warranty
- FCC Compliant

Camera, Shaft, and Base Unit



LCD Monitor



Specifications

CAMERA	
Imaging Sensor:	CMOS
Total Pixels:	712 x 486
Horizontal View Angle:	50°
Transmission Frequency:	2468 MHz
Modulation Type:	FM
Bandwidth:	18 MHz
Power Supply:	4 x AA Batteries
Weight (With Shaft):	1.17 lbs.
Operating Temperature:	14°F ~ 122°F
Operating Humidity:	15 ~ 85% RH
Diameter (mm/inches)	15.9 / 0.63

MONITOR	
Screen Type:	2.36" LCD
Effective Pixels:	480 x 240
Video System:	NTSC
Transmission Frequency:	2468 MHz
Exterior Supply Voltage:	8V - 36V _{DC}
Consumption Current (Max.):	450 mA
Video Output Level:	0.9 - 1.3V _{P-P} @ 75 ohm
Dimensions (W x D x H) (inches):	3.94 x 2.76 x 1.18
Weight:	0.31 lbs.
Operating Temperature:	14°F ~ 122°F
Operating Humidity:	15 ~ 85% RH

* All specifications are subject to change without prior notice

Accessories Available:

WIC-10:
New Smaller 9mm
Camera Head



WIC-4:
3.28 Ft. Extension Shaft
(Add up to Three!)

