









REV.	DATE	DESCRIPTION
A	09/04/01	MODIFY BODY DIMENSION TO .625" [15.87]



RECOMMENDED
MOUNTING HOLE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE	 Connex Corporation			
1 BODY	BRASS	NICKEL	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	DRAWN	09/04/01	TITLE MINI-UHF BULKHEAD CRIMP JACK (FOR 174/U, 188/U, 316/U CABLE) (FOR 174/U, 188/U, 316/U CABLE)			
2 INSULATOR	TEFLON	NATURAL		CHECKED					
3 BARREL	BRASS	NICKEL		ISSUED					
4 CONTACT PIN	PHOS. BRONZE	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4			SIZE FSCM NO. 99001 DWS. NO. 182317.DWG			
5 SLEEVE	DELTRIN	NATURAL							
6 FERRULE	BRASS	NICKEL							
7						SCALE	NA	PART NO.	182317
8			DO NOT SCALE DRAWING			SHEET	1	OF	1