


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------------------|----------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 07/23/03 | MCCORMICK |
| B | ECN 3277: UPDATE DWG FORMAT | 4/10/08 | D.GRIFFIN |
| C | ECN 4383: CN RELEASE | 2/1/10 | D. CASTRO |





| MODEL # | LENGTH | | DIM "A" INCHES [MM] |
|-----------|--------|--------|---------------------------------|
| | FEET | METERS | |
| CCR2MM-2 | 2.0 | 0.61 | 3.0 \pm .3 [76.2 \pm 7.62] |
| CCR2MM-3 | 3.0 | 0.91 | 6.0 \pm .3 [152.4 \pm 7.62] |
| CCR2MM-6 | 6.0 | 1.83 | 6.0 \pm .3 [152.4 \pm 7.62] |
| CCR2MM-9 | 9.0 | 2.74 | 6.0 \pm .3 [152.4 \pm 7.62] |
| CCR2MM-12 | 12.0 | 3.66 | 6.0 \pm .3 [152.4 \pm 7.62] |
| CCR2MM-25 | 25.0 | 7.62 | 6.0 \pm .3 [152.4 \pm 7.62] |

RoHS Compliant ✓

NOTES:

1. L-COM LOGO IS REQUIRED ON BOTH SIDES OF MOLDED HOODS AND STRAIN RELIEFS.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

| | | | | | |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------|------------------|--------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ±.005 PROJECTION  | APPROVALS | DATE |  45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | | |
| | DRAWN BY C.MCCORMICK | 07/16/2003 | | | |
| | CHECKED BY D.PARHAM | 07/22/2003 | CATEGORY | AUDIO/VIDEO | |
| | APPROVED BY R.CARRICK | 07/22/2003 | | | |
| CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | PRODUCT DESCRIPTION | | | | |
| | DUAL RCA CABLE ASSEMBLY | | | | |
| | SIZE A | FSCM NO. 43321 | DWG. NO. CCR2MM | REV. C | |
| COLOR VARIATIONS MAY OCCUR | SCALE: NONE | | CAD FILE: CCR2MM.SLDDRW | | SHEET 1 OF 1 |