

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0457730001

Status:


Active

Overview:

Micro-Fit Connector System

Description:

Micro-Fit 3.0 Crimp Terminal, Female, with Lubricant, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Reel



- Documents:
- Drawing (PDF)

Product Specification PS-43045-001 (PDF)

Product Specification PS-43650-001 (PDF)

Packaging Specification PK-45773-001-001 (PDF)

Test Summary TS-43045-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	45773
Application	Power
Crimp Quality Equipment	Yes
Overview	Micro-Fit Connector System
Product Name	Micro-Fit 3.0
UPC	822350359955
Physical	
Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.061/g
Packaging Type	Reel
Plating min - Mating	0.102µm
Plating min - Termination	0.102µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	20, 22, 24
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	8.5A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-45773-001-001
Product Specification	PS-43045-001, PS-43650-001
Sales Drawing	SD-45773-001
Test Summary	TS-43045-001-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2020)4578-DC (25

June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

- Search Parts in this Series

45773 Series
- Mates With

43031 Micro-Fit 3.0 Male Crimp Terminals
- Use With

43025 , 43645 Micro-Fit 3.0 Receptacle Housings, 44133 Micro-Fit BMI Panel Mount Receptacle Housings

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	11030043
Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp	638120800

Terminals, 20-30
AWG
Hand Crimp Tool [638190000](#)
FineAdjust Applicator[639004500](#)
for Insulation OD
1.30-1.85mm, 20-24
AWG Wire
FineAdjust Applicator[639018800](#)
for Insulation OD
1.10-1.30mm - 20-24
AWG
FineAdjust Applicator[639018900](#)
for Insulation OD
0.91-1.09mm - 20-24
AWG
T2 Terminator [639104500](#)
for Insulation OD
1.30-1.85mm, 20-24
AWG
T2 Terminator [639118800](#)
for insulation OD
1.10-1.30mm - 20-24
AWG
T2 Terminator [639118900](#)
for insulation OD
0.91-1.09mm - 20-24
AWG