






**GUARDIAN®**

**Enclosed Relays**

## 1360PC/1365PC SERIES - DPDT

- DPDT (2C)
- Rated: 5 amps at 30 VDC and 120 VAC Resistive load, 1/8 H.P., 120 VAC
- Termination suitable for socket or Printed circuit
- Standard/stock AC coil voltages 24, 120
- Standard/stock DC coil voltage 12, 24
- Sockets available
- Weight 1 oz. (28 grams)





**5 AMPS**


| Coil Voltage | Coil Res. $\Omega$ | PART NUMBERS   |
|--------------|--------------------|----------------|
| 24 VAC       | 150                | 1360PC-2C-24A  |
| 120 VAC      | 3500               | 1360PC-2C-120A |
| 12 VDC       | 150                | 1365PC-2C-12D  |
| 24 VDC       | 600                | 1365PC-2C-24D  |

## 1330/1335 SERIES - DPDT

- DPDT (2C)
- Rated: 5 amps at 30 VDC & 120 VAC Resistive load; 3 amps at 120 VAC Inductive load; 1/8 H.P., 120 VAC.
- Sealed versions 1330S & 1335S
- Plug in/solder lug terminals 1330 & 1335
- Printed circuit terminals 1330P & 1335P
- Standard/stock AC coil voltages (1330) 12, 24, 120
- Standard/stock DC coil voltages (1335) 12, 24
- Sockets available
- Weight .75 oz. (21 grams)



**CIRCUIT DIAGRAM**






**5 AMPS**

| Coil Voltage | Coil Res. $\Omega$ | PART NUMBERS |               |                |
|--------------|--------------------|--------------|---------------|----------------|
|              |                    | Plug In      | P.C.          | P.C. Sealed    |
| 12VAC        | 49.5               | 1330-2C-12A  | 1330P-2C-12A  | 1330PS-2C-12A  |
| 24VAC        | 245                | 1330-2C-24A  | 1330P-2C-24A  | 1330PS-2C-24A  |
| 120VAC       | 5400               | 1330-2C-120A | 1330P-2C-120A | 1330PS-2C-120A |
| 12VDC        | 125                | 1335-2C-12D  | 1335P-2C-12D  | 1335PS-2C-12D  |
| 24VDC        | 500                | 1335-2C-24D  | 1335P-2C-24D  | 1335PS-2C-24D  |

## 1310/1315 SERIES - DPDT & 4 PDT

- 4PDT (4C) or DPDT (2C)
- Rated: 5 amps at 30 VDC & 120 VAC Resistive load, 3 amps at 120 VAC Inductive load; 1/8 H.P., 120 VAC.
- Sealed versions 1310PS, 1315PS
- Plug in/solder lug terminals 1310, 1315
- Printed circuit terminal 1310P, 1315P
- Standard/stock AC coil voltages (1310) 12, 24, 120
- Standard/stock DC coil voltages (1315) 12, 24, 110
- Sockets available
- Weight 1.52 oz. (43 grams)



**5 AMPS**

### 4PDT

| Coil Voltage | Coil Res. $\Omega$ | PART NUMBERS |               |                |
|--------------|--------------------|--------------|---------------|----------------|
|              |                    | Plug In      | P.C.          | P.C. Sealed    |
| 12VAC        | 45                 | 1310-4C-12A  | 1310P-4C-12A  | 1310PS-4C-12A  |
| 24VAC        | 160                | 1310-4C-24A  | 1310P-4C-24A  | 1310PS-4C-24A  |
| 120VAC       | 3900               | 1310-4C-120A | 1310P-4C-120A | 1310PS-4C-120A |
| 12VDC        | 160                | 1315-4C-12D  | 1315P-4C-12D  | 1315PS-4C-12D  |
| 24VDC        | 650                | 1315-4C-24D  | 1315P-4C-24D  | 1315PS-4C-24D  |
| 110VDC       | 11000              | 1315-4C-110D | 1315P-4C-110D | 1315PS-4C-110D |

### DPDT

| Coil Voltage | Coil Res. $\Omega$ | PART NUMBERS |               |
|--------------|--------------------|--------------|---------------|
|              |                    | Plug In      | P.C.          |
| 12VAC        | 45                 | 1310-2C-12A  | 1310P-2C-12A  |
| 24VAC        | 160                | 1310-2C-24A  | 1310P-2C-24A  |
| 120VAC       | 3900               | 1310-2C-120A | 1310P-2C-120A |
| 12VDC        | 160                | 1315-2C-12D  | 1315P-2C-12D  |
| 24VDC        | 650                | 1315-2C-24D  | 1315P-2C-24D  |
| 110VDC       | 11000              | 1315-2C-110D | 1315P-2C-110D |