



**Consult Heyco
for Window Tints
Other Than Clear.**



Heyco® Window Plugs

Mounting Hole Diameter Range: .187" (4,7 mm) to 2.000" (50,8 mm)



- Molded of **transparent** polycarbonate for internal viewing or light transmission.
- Snap into mounting holes with fingertip pressure—no tools required.
- Multiple sizes for use in .187" (4,7 mm) to 2.000" (50,8 mm) diameter holes.
- Lock firmly into panel up to .125" (3,2 mm) thick.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Approximate Head Thickness: .062" (1,6 mm). Thickness may vary.
- **Available in a variety of tints—consult Heyco.**

MOUNTING HOLE DIAMETER		PART NO. Clear*	DESCRIPTION	PART DIMENSIONS			
in.	mm.			A Head Diameter		B Overall Height	
				in.	mm.	in.	mm.
Single Locking Step for Panel Thickness up to .062" (1,6 mm)							
.187	4,7	1300	WP 187	.250	6,4	.234	5,9
.250	6,4	1301	WP 250	.312	7,9	.312	7,9
.312	7,9	1302	WP 312	.375	9,5		
Multiple Locking Steps for Panel Thickness up to .125" (3,2 mm)							
.375	9,5	1303	WP 375	.468	11,9	.406	10,3
.437	11,1	1304	WP 437	.531	13,5		
.500	12,7	1305	WP 500	.563	14,3		
.625	15,9	1307	WP 625	.734	18,6		
.750	19,1	1309	WP 750	.859	21,8	.453	11,5
.875	22,2	1311	WP 875	.953	24,2		
1.000	25,4	1312	WP 1000	1.125	28,6		
1.093 - 1.125	27,8 - 28,6	1313	WP 1093	1.218	30,9		
1.375	34,9	1314	WP 1375	1.500	38,1		
1.500	38,1	1316	WP 1500	1.620	41,2		
1.750	44,5	1318	WP 1750	1.875	47,6		
2.000	50,8	1319	WP 2000	2.157	54,8		

*Consult Heyco for Window Plugs in tinted colors.



SINGLE PANEL THICKNESS DESIGN



MULTIPLE PANEL THICKNESS DESIGN

*Quick
Specs*

Material Polycarbonate
Flammability Rating 94V-2
Temperature Rating -40°F (-40°C) to 239°F (115°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[9681](#) [9682](#) [9682T](#) [9683](#) [9683T](#) [9684](#) [9684T](#) [9685](#) [9686](#) [9686T](#) [9687](#) [9687T](#) [9688](#) [9688T](#) [9680](#)