

GPS Antennas

Stock Locator



- Monitor location with GPS models available in NMO, magnetic, and trunk mount options
- Multiple applications - heavy equipment to luxury automobiles
- Heavy duty spring available on some models
- GPSDS1370P model is ideal for ORBCOMM® applications.

Results 1 - 21 of 21

Item #	Model	Description	Center Frequency	Gain	Overall Height	Coax
GPS1575P	Standard AVL	Low Profile AVL	1575.42 MHz	26 dB	1.25 inches	RG174
GPSD4503P	Dual-Band GPS/Land Based AVL	Low Profile AVL w/Phantom	450 - 470 MHz	3 dB-MEG	3.5 inches	ATX195
GPSD7463P	Dual-Band GPS/Land Based AVL	Low Profile AVL w/Phantom	746 - 786 MHz	3 dB-MEG	1.25 inches	ATX195
GPSD8063P	Dual-Band GPS/Land Based AVL	Low Profile AVL w/Phantom	806 - 866 MHz	3 dB-MEG	1.25 inches	ATX195
GPSD8213P	Dual-Band GPS/Land Based AVL	Low Profile AVL w/Phantom	821 - 896 MHz	3 dB-MEG	1.25 inches	ATX195
GPSD8903P	Dual-Band GPS/Land Based AVL	Low Profile AVL w/Phantom	890 - 960 MHz	3 dB-MEG	1.25 inches	ATX195
GPSD9023P	Dual-Band GPS/Land Based AVL	Low Profile AVL w/Phantom	806 - 866 MHz	3 dB-MEG	1.25 inches	ATX195
GPSDS1370G	Survivor™	Survivor - VHF/GPS w/ Magnetic Base	137 - 150 MHz	Unity	7.25 inches	14'
GPSDS1370P	Survivor™	Survivor - VHF plus GPS	137 - 150 MHz	Unity	21.75 inches	14'
GPSDS1370PLP	Survivor™	Survivor - Low Profile VHF plus GPS	137 - 150 MHz	Unity	7.25 inches	14'
GPSDS8060P	Survivor™	Survivor - 800 MHz + Unity Gain	806 - 866 MHz	Unity	6 inches	14'
GPSDS8063P	Survivor™	Survivor - 800 MHz + 3 db Gain	806 - 866 MHz	3 dB	14.285 inches	14'
GPSDS8065P	Survivor™	Survivor - 800 MHz + 5 db Gain	806 - 866 MHz	5 dB	26.25 inches	14'
GPSIM15	Quad-Band MicroBlade™ with and without GPS	Internal GPS Antenna - 3 volt	N/A	GPS: 2.5 dBi	N/A	5 ft
GPSNMOAO	GPS Add On Bracket	Bright Stainless Bracket with GPS	1575.42 MHz	N/A	0.75 inches	17' RG-174
GPSS380DP26-001	Survivor™	Survivor - heavy duty commercial vehicular ante	380 - 430 MHz	2.8 dB	7.17 inches	N/A
GPST821/18503P	Tri-Band GPS AVL	Cell/PCS/GPS Low Profile AVL	1850 - 1990 MHz 821 - 896 MHz	3 dB-MEG	1.25 inches	17' RG-174
GPSU15M	NMO Mountable	NMO GPS - 3 or 5 Volt Bias	1575.42 MHz	26 dB	1.5 inches	N/A
GPSUW15M	NMO Mountable	NMO GPS - 3 or 5 Volt Bias - White	1575.42 MHz	26 dB	1.5 inches	N/A
TM8GPS	Trunk Mount GPS	Trunk Mount GPS	1575.42 MHz	N/A	0.75 inches	N/A
TMB8GPS	Trunk Mount GPS	Black Trunk Mount GPS	1575.42 MHz	N/A	0.75 inches	N/A

Results 1 - 21 of 21