



Notes:

- Insulator
PPS, UL 94V-0
Contacts
Phosphor Bronze
Matte Tin Plated 150U" over Nickel
Current Rating
1A
Insulating Resistance
10000M ohm Min.
Withstanding Voltage
1000V AC
Contact Resistance
15m ohm Max.
Operating Temperature
-40 Degree to +105 Degree

A-CCSxx-x-xxx-R
└┐└┐└┐
1 2 3

1. No. of Contacts
20/28/32/44/52/68/84
2. Finish
z - Tin
G - Gold
3. Version
SM : without polarizing peg, tube packing



Description

Name:	Approval.:
A-CCSxx-x-xxx-R	Check.: Ahmaa Feb.23,06
Chip-carrier-sockets,SMD	Draw.: Alex Feb.23,06
ASSMANN	Rev.: 01
Electronic Components	Unit: mm
	Sheet: 1/1

		Dimension					
No. of Contacts	Quantity in tube	A	B	C	D	E	F
20	39	15,34	15,34	5,08	5,08	10,03	10,03
28	33	17,85	17,85	7,62	7,62	12,57	12,57
32	29	17,85	20,42	7,62	10,16	12,57	15,11
44	26	23,07	23,07	12,70	12,70	17,65	17,65
52	23	25,50	25,50	15,24	15,24	20,19	20,19
68	19	31,00	31,00	20,32	20,32	25,27	25,27
84	16	36,10	36,10	25,40	25,40	30,35	30,35