




# Long collets for unscreened cable «U» for connector styles S, SV, SOV, K, DK

| Cable Dia.<br>Range | Collet Dia.<br>for ordering | P/N for Packaged Collet (only for separate ordering) ① |
|---------------------|-----------------------------|--------------------------------------------------------|
| 2.2 - 3.2           | 3.2                         | Collet «A»<br>103.252                                  |
| 3.2 - 4.2           | 4.2                         | 103.1414                                               |
| 4.2 - 4.7           | 4.7                         | 103.1413                                               |
| 4.7 - 5.2           | 5.2                         | 103.253                                                |
| 5.2 - 5.7           | 5.7                         | 103.238                                                |
| 5.7 - 6.2           | 6.2                         | 103.251                                                |
| 6.2 - 6.7           | 6.7                         | 103.1409                                               |
|                     |                             | 103.250                                                |
|                     |                             | 103.1408                                               |



Sleeve «A» for connectors with PTFE insulator, P/N 103.1289

Sleeve «B» for connectors  
with moulded insulators, P/N 103.1407



P/N required for separate ordering only


| Cable Dia.<br>Range | Collet Dia.<br>for ordering | Collet ①      | Seal ②   | Washer ③ | Ring ④   | Set ①-⑤ packaged in tube ①<br>with Sleeve «A» | with Sleeve «B»   |
|---------------------|-----------------------------|---------------|----------|----------|----------|-----------------------------------------------|-------------------|
| 1.7 - 2.2           | 2.2                         | E32 103.2/2.2 | 103.1536 | 103.1535 | 103.1256 | E31 103.2/2.2 + A                             | E31 103.2/2.2 + B |
| 2.2 - 2.7           | 2.7                         | E32 103.2/2.7 | 103.1536 | 103.1534 | 103.1256 | E31 103.2/2.7 + A                             | E31 103.2/2.7 + B |
| 2.7 - 3.2           | 3.2                         | E32 103.2/3.2 | 103.1270 | 103.1263 | 103.1255 | E31 103.2/3.2 + A                             | E31 103.2/3.2 + B |
| 3.2 - 3.7           | 3.7                         | E32 103.2/3.7 | 103.1269 | 103.1262 | 103.1255 | E31 103.2/3.7 + A                             | E31 103.2/3.7 + B |
| 3.7 - 4.2           | 4.2                         | E32 103.2/4.2 | 103.1268 | 103.1261 | 103.1254 | E31 103.2/4.2 + A                             | E31 103.2/4.2 + B |
| 4.2 - 4.7           | 4.7                         | E32 103.2/4.7 | 103.1267 | 103.1260 | 103.1253 | E31 103.2/4.7 + A                             | E31 103.2/4.7 + B |
| 4.7 - 5.2           | 5.2                         | E32 103.2/5.2 | 103.1266 | 103.1259 | 103.1252 | E31 103.2/5.2 + A                             | E31 103.2/5.2 + B |
| 5.2 - 5.7           | 5.7                         | E32 103.2/5.7 | 103.1265 | 103.1258 | 103.1251 | E31 103.2/5.7 + A                             | E31 103.2/5.7 + B |
| 5.7 - 6.2           | 6.2                         | E32 103.2/6.2 | 103.1264 | 103.1257 | 103.1250 | E31 103.2/6.2 + A                             | E31 103.2/6.2 + B |

① We have begun shipping the cable clamp assemblies in a disposable plastic tube.  
In this case, a disposable internal retainer keeps the contact block in place.  
For details see page L6 and «General Cable Assembly Instructions» on page N2.



2

① We have  
in this c  
For deta


Long  
for con  
Cable  
Ran  
2.2  
2.7  
3.2  
3.7  
4.2  
4.7  
5.2  
5.7  
6.2




## CRIMP CONTACTS





6. Slide the ring to the front end
7. Bend cable screen outwards
8. Insert half shell and retain with the ring




2



## SOLDER CONTACTS



12. Screw clamp nut to the body and tighten by means of wrenches (see pages O and P)



S - Short collet  
E - Sealed version

All dime  
All strip  
adjusted

965 194

26557

|               |   |     |     |
|---------------|---|-----|-----|
| 102 A002      | S | 9.5 | 12  |
|               | E | 9.5 | 12  |
| 102 A017      | S | 6   | 8.5 |
| 102 Z017      | E | 5   | 7   |
| 102 A018      | S | 9.5 | 12  |
| 102 Z018      |   |     |     |
| 102 A025      | S | 21  | 29  |
| 102 Z025      |   |     |     |
| (RG 58 cable) |   |     |     |