



REV.	DATE	DESCRIPTION
A	01/25/99	ADD MOUNTING HOLE DIMENSION
B	06/14/07	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	G.R.S.	06/14/07							
7						CHECKED				PART DESCRIPTION F STRAIGHT RECEPTACLE – EXTENDED CONTACT —					
6						ISSUED									
5	GASKET	N.B.R.	BLACK	1	DO NOT SCALE DRAWING	SHEET	1 OF 1				PART NO. 222144				
4	INSULATOR	DELTRIN	NATURAL	1											
3	CONTACT PIN	BRASS	BRIGHT TIN	1						DWG. NO. 222144.DWG					
2	INSULATOR	P.P	NATURAL	1											
1	BODY	BRASS	NICKEL	1		CAD FILE		C:/222/222144.DWG		REV.	B	SIZE	A	SCALE	NA
DESCRIPTION															
MATERIAL															
FINISH															
QTY															