


**MALLORY****Mallory Sonalert Products Inc.**Part # **PB-12N23P-12****Sales Outline Drawing**Revision **A****OBSOLETE- USE PB-12N23P-12Q****Specifics**

Oscillation Frequency (Hz)	2300 $\pm$ 400
Operating Voltage (Vdc)	9.0 $\sim$ 15
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	50 at Rated Voltage
Sound Pressure Level Min. (dB)	85 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 $\sim$ +70
Storage Temperature (°C)	-30 $\sim$ +80
Housing	PPO plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	1.8
Options	For other options contact factory

PS: V<sub>p-p</sub> = 1/2duty, square wave**Dimensions:** (units: mm)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PB-12N23P-12](#)