




## 936060-2 Product Details

[Share](#) | [Print](#) | [Email](#)

**936060-2**

### SSC (Sealed Sensor Connector) System


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Wire-to-Device
- Connector
- Housing
- Connector Style = Plug
- Contact Type = Socket

[View all Features](#)

TE Internal Number: 936060-2


[View 3D PDF](#)
[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- None Available

##### Additional Information:

- [Product Line Information](#)

##### Catalog Pages/Data Sheets:

- None Available

##### Related Products:

- [Tooling](#)

##### Product Specifications:

- None Available

##### Application Specifications:

- None Available

##### Instruction Sheets:

- None Available

##### CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version C\)](#)
- [3D Model \(IGES, Version C\)](#)
- [3D Model \(STEP, Version C\)](#)

[List all Documents](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- Product Type = Connector
- Connector Type = Housing
- Wire/Cable Type = FLR (Thin Walled Cable)
- Sealed = Yes
- Termination Method to Wire/Cable = Crimp
- Strain Relief = Without

##### Contact Features:

- Contact Type = Socket
- Circuit Number(s) Blocked = None

##### Mechanical Attachment:

- Keying = Code I
- Panel Mount Retention = Without
- Mating Retention Type = Latching

##### Housing Features:

- Connector Style = Plug
- Housing Material = PA66 - GF15
- Housing Color = Black
- Mating Alignment = With
- Mating Alignment Type = Keyed

##### Electrical Characteristics:

- Contact - Rated Current (A) = 10
- Operating Voltage Reference = AC/DC
- Operating Voltage (VAC) = 125
- Operating Voltage (VDC) = 125

##### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- Agency/Standard = IEC 664/664A (DIN VDE 0110)

##### Termination Features:

- Wire/Cable Size (AWG) = 13.5 - 15.5, 17 - 20
- Wire/Cable Size (mm<sup>2</sup>) = 0.5 - 1, 1.25 - 2.5
- Seal Type = Seal Ring

##### Environmental:

- Operating Temperature (°C [°F]) = -40 - +150 [-40 - +302]

##### Dimensions:

- Profile Height (Y-Axis) (mm [in]) = 20.10 [0.791]

##### Conditions for Usage:

- Accepts Wire Insulation Diameter, Range (mm [in]) = 1.40 - 2.10 [0.055 - 0.083], 2.20 - 3.00 [0.0866 - 0.118]
- Applies To = Wire/Cable

##### Body Features:

- Wire Type = Stranded
- Number of Positions = 3
- Number of Rows = 1
- Seal Material = Silicone
- Seal Color = Ultramarine Blue
- Mating Retention = With
- Length (X-Axis) (mm [in]) = 30.50 [1.2007]
- Width (Z-Axis) (mm [in]) = 30.00 [1.181]

##### Operation/Application:

- Application Use = Wire-to-Device
- Contact Transmits (Typical Application) = Power

##### Packaging Features:

- Packaging Method = Bag
- Packaging Quantity = 150

##### Other:

- GET 0.64 Connector System = No
- Brand = Tyco Electronics
- Comment = See drawing for additional product information.; Refer to the application and product specification for additional information.

#### Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events &amp; Technology Updates

 Enter your email address 

[Provide Website Feedback](#)