



WATERTIGHT



Pelican Protector Watertight Equipment Cases

Watertight and airtight to 30 feet for the ultimate in protection. Constructed of lightweight space age structural resin with a neoprene O-ring seal and exclusive purge valve. Supplied complete with pre-scored pick-n-pluck foam or padded dividers (no cutting required). Also includes locking flanges, massive multiple latches for absolute security and a comfortable molded fold down handle. Custom colors and foam inserts fabricated on special order. #1700 and #1750 supplied with regular foam, pick-n-pluck is not available. 1470cc #1 includes lid organizer, fitted shock absorbing tray and removable shoulder strap. 1470cc #2 includes lid organizer, high Density Pick 'n Pluck Foam and removable shoulder strap.

Platt Part #	Inside Dim. (L)	Inside Dim. (W)	Inside Dim. (D)	Outside Dim. (L)	Outside Dim. (W)	Outside Dim. (D)
1010	4.4375	2.9375	1.6875	5.4375	4.0625	2.125
1020	5.375	3.625	1.6875	6.375	4.75	2.125
1030	6.5	2.75	2.0625	7.5	3.875	2.4375
1040	6.5625	3.9375	1.75	7.5	5.0625	2.125
1050	6.5625	3.9375	2.75	7.5	5.0625	3.125
1060	8.4375	4.4375	2.25	9.375	5.5625	2.625
1120	7.375	4.875	3.062	8.25	6.56	3.56
1150	8.375	5.875	3.6875	9.25	7.56	4.375
1200	9.375	7.25	4.062	10.625	9.6875	6.875



1300	9.375	7.25	6.125	10.625	9.6875	6.875
1400	12	9.0625	5.1875	13.375	11.625	6
1420	13	5	10	15	8.5	10.5
1450	14.8125	10.375	6	16	13	6.875
1470	15.75	10.5625	3.75	16.6875	13.0625	4.375
1470ac	15.75	10.5625	3.75	16.6875	13.0625	4.375
1470cc #1	16	10.75	4	16.75	13.25	4.375
1470cc #2	15.75	10.5625	3.75	16.6875	13.0625	4.375
1490	18.875	11.5	4.125	19.4375	13.9375	4.6875
1490AC	17.875	11.5	4.125	19.4375	13.9375	4.6875
1490cc	18.875	11.5	4.125	19.4375	13.9375	4.6875
1500	17	11.4375	8.125	18.5	14.0625	6.9375
1504	17	11	6.125	18.5	14.063	6.875
1520	17.875	12.875	6.75	19.125	15.4375	7.5625
1524	17.875	12.75	6.75	19.125	15.438	7.563
1526	17.875	12.75	6.75	19.125	15.438	7.563
1527	17.75	13.5	7.25	19.125	15.438	7.563
1550	20.0068	14.9375	7.75	20.0068	16.1875	8.5625
1600	21.75	16.4375	7.875	24.25	19.4375	8.6875
1610	22.25	17	10.5	24.25	19.5	12
1620	22.25	17.125	12.625	24.625	19.625	14
1650	29	17.875	10.5	32.5	20.5	11.3125
1700	35.75	13.8125	5.25	38.125	17.8125	6.125
1750	50.5	13.4375	5.25	53	17.4375	6.0625

PELICAN FEATURES

All watertight cases feature lightweight space-age structural resin, O-Ring sealed, atmospheric purge valve, unconditional lifetime guarantee of excellence. Made in USA.

PELICAN 100% GUARANTEE

Unconditional lifetime guarantee of excellence by Pelican Products, Inc. Warranty and additional information available through your local dealer or call 1-800-99-PLATT (997-5288) or visit our webpage. www.plattcases.com.

Pelican case is available as a toolcase. Click [Here](#) for more information.