

NPN TRANSISTORS

IC Amps Max	V _{CEO} (sus) Volts Min	Device Type	hFE @ IC Min	Amps	ft MHz	Watts	PD @ TC °C	Case JEDEC
2	80	2N4300	15	2.0	30	15	100	TO-5
		2N4998	30	1.0	50	30	25	TO-111
		2N5000	70	1.0	60	30	25	TO-111
3	150	SFT4300	50	2.0	100	15	100	TO-5
	40	2N3867	25	2.5	60	6	25	TO-5
	60	2N5334	30	1.0	40	6	25	TO-39
	80	2N5335	30	1.0	40	6	25	TO-39
	150	SFT3507	30	3.0	60	5	25	TO-5
5	80	2N5152	30	2.5	60	10	50	TO-5
		2N5154	70	2.5	70	10	50	TO-5
		2N3996	40	1.0	40	30	100	TO-111
		2N3997	80	1.0	40	30	100	TO-111
		SFT3997	80	1.0	80	30	100	TO-59
		2N5336	30	2.0	30	6	25	TO-39
		2N5337	30	2.0	30	6	25	TO-39
		2N5002	30	2.5	60	50	50	TO-59
		2N5004	70	2.5	70	50	50	TO-59
	100	2N5338	30	2.0	30	6	25	TO-5
		2N5339	60	2.0	30	6	25	TO-5
	120	SFD5390 †	1000	5.0	40	15	100	TO-33
	150	SFT502	30	2.5	80	10	50	TO-5
		SFT504	50	2.5	80	10	50	TO-5
10	80	2N5006	30	5.0	35	100	50	TO-61
		2N5008	70	5.0	40	100	50	TO-61
		2N5659	50	5.0	30	30	100	TO-111
	150	SFT6200	50	5.0	100	10	25	TO-5
	150	SFT5659	50	5.0	70	30	25	TO-59
15	90	2N3265	20	15	20	125	25	TO-63
20	90	2N5330	40	10	80	80	100	TO-61
	120	SFT5671	20	30	30	150	25	TO-3*
	140	SFT5672	20	30	30	150	25	TO-3*
	200	2N6322	6	30	10	200	100	TO-3
		2N6324	6	30	10	200	100	TO-63
30	120	SFT5671	10	50	50	150	25	TO-3*
	140	SFT5672	10	50	50			
	140	SFT815	15	90	10	300	50	TO-3*
50	100	SFT1010	7	100	35	300	50	TO-3*
	120	SFT1012	7	100	35	300	50	TO-3*
	140	SFT1014	7	100	35	300	50	TO-3*
	150	SFT1002	10	50	50	200	25	TO-3*
		SFT1004	25	50	50	200	25	TO-3*
90	160	SFT1016	7	100	40	300	50	TO-3*
	180	SFT1018	7	100	40	300	50	TO-3*
	200	SFT1020	7	100	40	300	50	TO-3*
	100	SFT2010	5	200	30	600	50	TO-3*
	120	SFT2012	5	200	30	600	50	TO-3*
100	140	SFT2014	5	200	30	600	50	TO-3*
200	100	SFT2010	5	200	30	600	50	TO-3*
	120	SFT2012	5	200	30	600	50	TO-3*
	140	SFT2014	5	200	30	600	50	TO-3*

†Darlington

* TO - 3 with 60 Mil Pins

Contact SSDI for higher voltage units.