



NOTES:


- 1. SUGGESTED MOUNTING HOLE = ϕ .191[4.86]
- 2. MTG. PREFORM IS 23-0007-6900.



LEAD FINISH: SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	470pF ±20%
TEMP. RANGE	-55°C TO 125°C
CURRENT	AMP MAX.
WORKING VOLTAGE	85°C VDC MAX. 125°C VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	N/A
10	N/A
100	N/A
1 GHz	N/A
10 GHz	N/A



MARKING:
PART: NONE
BAG:
54-803-004-471M
DATE CODE
QTY./BAG (200 MAX.)

		CN. 185169 00	REV. 1 CHANGE NOTICE NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED		 SPECTRUM CONTROL INC.	ERIE, FAIRVIEW PENNSYLVANIA		
				Fraction 1/64			DwnKAUFFMAN	Description	
				Dec. .xx±					
				Dec. .xxx±0.15					
				Angles ±0° 30'			Ckd.8-10-98	CERAMIC FILTER	
		CN. 185169 00	REV. 1 CHANGE NOTICE NO.	CODE IDENT. NO.		Apvd.	54803004X5R471M		
				OLSP2		Scale			