

Product Description

BS.R20PB : Rolling Probag

❑ HIGH QUALITY AND DURABILITY

- High resistant fabric : 1200*1200 deniers; polyester with pvc backing for abrasion and water resistance ; Easy-sliding and heavy-duty zippers
- Polypropylene Bottom : Waterproof, Stand-up function, « non agressive » for fragile floors

❑ EXTREMELY COMFORTABLE

- Leather grip
- Shoulder strap with reinforcing cushion for shoulder
- Air-mesh back and shoulder
- Protective cover

❑ EFFICIENT TOOLS ORGANIZATION

- 6 external pockets
- 1 special pocket for handsaw (603F) same inner organization as BS.T20
- One additional large pocket for documents (A4) or for cover
- Great accessibility to the tools

❑ EASY TO USE

- Telescopic handle
- toothed wheels

1200*1200 deniers

Capacity : 33 liters

Load resistance : 12 kg

Dimensions : L470x P240 x H30 mm

Outside dimensions : L550xP360xH440mm



Your rolling Probag!