


**Part Number: 70573-0116**

2.54mm Pitch SL™ Header, Single Row, Right Angle, 4.57mm Pocket, Shrouded, 12 Circuits, 0.76µm Gold (Au) Selective Plating, Tin (Sn) PC Tail Plating

*Series Image - Reference only*

<b>Status:</b>	<b>OBsolete</b>
<b>Replacement:</b>	<a href="#">70575</a> (similar)
<b>Series:</b>	<a href="#">70573</a>
<b>Category:</b>	PCB Headers

**Product Environmental Compliance**[EU RoHS](#): Compliance Status Not Reviewed[China RoHS](#):[REACH SVHC](#): Not Reviewed[Low-Halogen Status](#): Not Reviewed**Part Detail****General**

<b>Status</b>	<b>Obsolete</b>
Category	PCB Headers
Series	<a href="#">70573</a>
Application	Signal, Wire-to-Board
Obsolete Date	2004/09/01
Product Name	SL™

**Physical**

Circuits (Loaded)	12
Circuits (maximum)	12
Glow-Wire Compliant	No
Number of Rows	1
Orientation	Right Angle
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully

**Material Info****Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)