

FJH-20-D-04.00-4

FJH-10-D-06.00-4

(0.50 mm) .0197"

FJH SERIES

FLAT FLEXIBLE CABLE (FFC) JUMPER

SPECIFICATIONS

For complete specifications
see www.samtec.com?FJH

Conductor:
Tin Plated Copper

Conductor:

Resistance:
1000 Ω /km max
Insulation Resistance:
10 M Ω /km min
(conductor-to-conductor)

Dielectric Test:

400 VAC during 1 minute
(conductor-to-conductor)

Temperature Rating:

-30 $^{\circ}$ C to +80 $^{\circ}$ C

Voltage Rating:

60 VAC

RoHS Compliant:

Yes


Mates with:
ZF5S

Double or
reversed ended

(0.50 mm)
.0197"
pitch

(4.00 mm)
.157"

FJH	NO. OF POSITIONS	STYLE	OVERALL LENGTH	STRIP LENGTH
	-10, -15, -20, -25, -30, -40, -43, -50	-D = Double End -R = Reversed End	-“XX.XX” = Specify OVERALL LENGTH in inches ($\pm 1/8$ inch) (-D & -R = (50.80 mm) 2.00" minimum)	-4 = (4.00 mm) .157"



Note: Stiffener color will be blue or black at Samtec's discretion.

Note: Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.