

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0745464080](#)
Status: **Active**
Overview: [iPass Connector System](#)
Description: 0.80mm Pitch iPass PCI Express X4-to-X8 Transition Cable Assembly, 0.50m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable Assemblies
Series [74546](#)
Assembly Configuration Dual Ended Connectors
Connector to Connector PCI Express-to-PCI Express
Overview [iPass Connector System](#)
Product Name iPass, PCI Express
UPC 191128125666

Physical
Cable Length 0.50m
Circuits (Loaded) 68
Gender Plug/Plug
Lock to Mating Part Yes
Material - Metal Zinc Alloy
Number of Rows 2
Packaging Type Bag
Pitch - Mating Interface 0.80mm
Single Ended No
Waterproof / Dustproof Yes
Wire Insulation Diameter N/A
Wire Size AWG 24, 26, 28
Wire/Cable Type Round

Electrical
Current - Maximum per Contact 1.0A
Shield Type Upper Shielding
Shielded Yes
Voltage - Maximum 30V DC

Material Info

Reference - Drawing Numbers
Sales Drawing SD-74546-408



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[74546](#) Series

Mates With
[75586](#) iPass Receptacle. [741500001](#) SMT Receptacle

Use With
[74540](#) PCIe Guide Frame

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION