



Circuit Board Indicators

Panel Mount Indicators

Solid State Lighting

Traffic Signals

Vehicle Lighting

Rail

Obstruction Lighting

Hazardous Area Lighting

Heliport Lighting

how to purchase

sales contacts

stock check

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:

search

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes

FAQs

Dialight Ltd (UK)

Dialight Garufo

Dialight BLP

LumiDrives

Circuit Board Indicators - Through Hole Indicators

P/N# 5511409F

Description

Package Options

Product Type

Sub Product Type

Configuration

Lamp Type

Viewing

Viewing Angle

Test Current (mA)

Forward Current (mA)

LED Centerline

Polarity

3 mm CBI Right Angle

100 Pieces Per Bag

Through Hole Indicators with Single Housing

3 mm Lens

Single Color

Right Angle

45

1mA

30mA

3.05

Cathode Right

Absolute Maximum Ratings

(Ta = 25 °)

Derating

Reverse Voltage

Solder Temp

Operating Temp

Storage Temp

from 50° @ .5 mA/°C

5 V

260° for 5 sec

-20 to +100° C

-55 to +100° C

RoHS /pB Free

view PDF

Operating Characteristics

LED Position

Color

Lamp Type

LED Type

Intensity Min (mcd)

Intensity Typ (mcd)

Intensity Max (mcd)

Fwd Voltage Min

Fwd Voltage Typ

Fwd Voltage Max

Dom Wavelength Min (nm)

Dom Wavelength Typ (nm)

Dom Wavelength Max (nm)

Power Dissipation Max (mW)

Backlighting

Pitch Between Vertical

Pitch Between Horizontal

Lum Intensity Min

Lum Intensity Typ

Lum Intensity Max

Red

Single Color

Low Current

2

3.0

87

Distributor Stock Check

Check stock with our distributors now.

5511409F

check stock

Distributor Stock Check

Check stock with our distributors now.

5511409F

[check stock](#)