


CLASS 2 FOOT MOUNT TRANSFORMERS – 40 & 50VA



APPLICATIONS:

- Commercial Dryers
- Deep Fryers
- Greenhouse Controls
- HVAC – Heating, Ventilation, Air Conditioning Systems
- Security Systems
- Video Games
- Automatic Doors
- Solar Heating Controls

AVAILABLE INPUT VOLTAGES:

- 120V, 208/240V and 120/208/240V

TRANSFORMER TERMINATIONS:

- 11" Color Coded Leads

FEATURES:

- Convenient Mounting Plate
- Protective Plastic Covers

GENERAL INFORMATION

Safety Agency Certification: **UL** U.S. U.L. File No. E33334



Recognized under Category XOKV2/XOKV8

NEC Classification: Class 2, Inherently Limited

U.L. Insulation Class: Class B (130°C Max)

Output Voltage: 24VAC

OUTLINE DRAWING



W-R PART NUMBER	STANCOR PART NUMBER	INPUT VOLTAGE	FREQ Hz	OUTPUT VOLTAGE	OUTPUT CURRENT	VA	MOUNTING	PRI TERM.	SEC TERM.	DIMENSIONS-INCHES				Wt. (Lbs)
										H	W	D	MW	
90-T40F1	T40-24F1	120	60	24	1.67	40	FOOT	LEADS	LEADS	2.75	3.25	2.19	2.81	1.36
90-T40F2	T40-24F2	208/240	50/60	24	1.67	40	FOOT	LEADS	LEADS	2.75	3.25	2.19	2.81	1.44
90-T40F3	T40-24F3	120/208/240	60	24	1.67	40	FOOT	LEADS	LEADS	2.75	3.25	2.19	2.81	1.44
90-T50F3	T50-24F3	120/208/240	60	24	2.08	50	FOOT	LEADS	LEADS	2.75	3.25	2.63	2.81	1.96