

**TIGER™
EYE
SYSTEM**



MH-130-02-L-D-LC



HIGH-RELIABLE HORIZONTAL

RV[®]
FILE NO. E111594

FSH	1	NO. PINS PER ROW	04	PLATING OPTION	ROW OPTION	OPTIONS
05, 10, 15, 20, 25 (-DH Option) 05, 10, 15, 20, 25, 30, 35, 40, 45 (-RA Option) (Standard sizes)				-F = Gold flash on post, Matte Tin on tail -L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail	-DH = Double Row Horizontal (Surface Mount) -RA = Right-angle (Through-hole)	-SL = Solder Locks -C = (4.50 mm) .177 DIA Polyimide film Pick & Place Pad (10 positions minimum) not available with -RA option -TR = Tape & Reel (Not available with -RA) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (Not available with -RA)

-FR
= Full Reel Tape & Reel
(must order max. quantity
per reel; contact Samtec
for quantity breaks)

**TIGER™
EYE**

Technical drawing of a mechanical part with dimensions:

- Top dimension: $(0.64) .025 \text{ TYP}$ with a downward arrow.
- Left side dimensions: $(4.57) .180$ with a vertical double-headed arrow.
- Right side dimensions: $(1.65) .065$ with a vertical double-headed arrow, and $(2.03) .080$ with a vertical double-headed arrow.

Diagram showing a cross-sectional view of the IC package with dimensions: (1.41) DIA, .056, (1.02), and .040.