

181-00241

Article Number: 181-00241

Slotted Wall Wiring Duct, 2" X 5", Non-Adhesive, PVC, White, 30ft/Box



Download drawing

Download spec sheet

Base Data

Local Order Number	181-00241
Type	SL2X5
Color	White (WH)
Features and Benefits	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
Product Description	Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "Ts".
Short Description	Slotted Wall Wiring Duct, 2" X 5", Non-Adhesive, PVC, White, 30ft/Box

Product Dimensions

Length L (Imperial)	6.0 ft
Length L (Metric)	1.83 m
Width W (Imperial)	2.0 "
Width W (Metric)	50.8 mm
Width W2 (Imperial)	2.0 "
Width W2 (Metric)	50.8 mm
Width W3 (Imperial)	0.4 "
Width W3 (Metric)	10.2 mm
Width W4 (imperial)	1.0 "
Width W4 (metric)	25.4 mm
Width W5 (imperial)	4.6 "
Width W5 (metric)	116.8 mm
Width W6 (imperial)	0.5 "
Width W6 (metric)	12.7 mm
Height H (Imperial)	5.07 "
Height H (Metric)	128.8 mm
Height H2 (Imperial)	2.0 "
Height H2 (Metric)	50.8 mm
Height H3 (imperial)	0.4 "
Height H3 (metric)	10.2 mm
Mounting Hole Centers (Imperial)	4.0 "

Logistics and Packaging

Quantity Per	box
Package Quantity	30.0 ft
Package Quantity (Metric)	9.1 m
Carton Quantity	120.0 ft

Material and Specifications

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	self-extinguishing
Operating Temperature	+122°F (+50°C)
ROHS Compliant	Yes
Certification/Specification	CSA UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No
UL Recognized (US)	Yes