



| PART NO.   | MAX NO. OF CONDUCTORS | "A"<br>±0.5 (.02) | "B"<br>±1.0 (.04) | "C"<br>REF | "D"<br>REF | "E"<br>±0.5 (.02) |
|------------|-----------------------|-------------------|-------------------|------------|------------|-------------------|
| FCW-29-01  | 30                    | 31.5 (1.24)       | 45.1 (1.78)       | 7.7 (.30)  | 11.1 (.44) | 18.9 (.74)        |
| FCW-30-01  |                       | 31.6 (1.24)       | 45.5 (1.79)       | 9.0 (.35)  | 13.1 (.52) | 19.1 (.75)        |
| FCW-40-01  | 40                    | 39.3 (1.55)       | 53.0 (2.09)       | 9.3 (.37)  | 13.4 (.53) |                   |
| FCW-50-01  | 50                    | 63.2 (2.49)       | 77.2 (3.04)       | 9.1 (.36)  | 13.2 (.52) | 18.9 (.74)        |
| FCW-50H-01 |                       | 64.6 (2.54)       | 78.2 (3.08)       | 15.0 (.59) | 19.0 (.75) |                   |



NOTES:

- 1.MATERIAL: NYLON 6/6 (RMS-01).  
FLAME RETARDANT NYLON 6/6 (RMS-19).  
AVAILABLE BY SPECIAL ORDER ONLY.
- 2.COLOR: NATURAL.
- 3.TAPE: 1.6(1/16) THICK, DOUBLE SIDE ADHESIVE (RMS-350).
- 4.ALTERNATE UNITS FOR REFERENCE ONLY

|                                                    |                         |               |                                                               |           |                                                                                       |                  |                                                                                       |
|----------------------------------------------------|-------------------------|---------------|---------------------------------------------------------------|-----------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|
| TITLE: FLAT CABLE CLAMP                            |                         |               |                                                               |           |  | DWG IN<br>MM[IN] |  |
| CREATED USING<br>SOLIDWORKS                        | FILE #: FCW             |               | DWN: J.T                                                      | APP: J.T  | FINAL                                                                                 |                  |                                                                                       |
| TOLERANCES<br>UNLESS NOTED<br>.X=±0.25<br>ANG.=±1° | SHEET: 1 OF 1           | SHEET SIZE: A | DT: 11.17.06                                                  | CHKD: W.H | PART #                                                                                | PRINT<br>TYPE    |                                                                                       |
|                                                    | RE: RICHCO XIAMEN<br>-- |               | RICHCO XIAMEN<br>RICHCO_XIAMEN@RICHCO.CN<br>(+86) 592-6884500 |           | SEE TABLE                                                                             | CA               |                                                                                       |

|      |                                         |       |          |
|------|-----------------------------------------|-------|----------|
| A    | RELEASED FOR PRODUCTION, SEE ECN XM0013 | J.T   | 06.07.07 |
| REV. | DESCRIPTION                             | ENGR. | DATE     |