

TY25MX

Premium cable tie with stainless steel locking barb - UV-resistant version, especially recommended for outdoor applications.

Catalog Number: TY25MX
EAN Number: 05414363062691
UPC Number: 78621082467
Description: Premium, standard cable tie, 186 x 4.8 mm, black Polyamide 6.6 UV-resistant



Technical Information

Type	standard
Material	Polyamide 6.6 UV-resistant
Material Locking Barb	316 grade stainless steel
Temperature Range	-40°C to +85°C
Flammability Rating	UL 94 V-2
Colour	black
Halogen free	yes
Silicone free	yes
UV-resistant	yes

Approvals

UL listed	E49405
Germanischer Lloyd approval	yes
Lloyds Register approval	yes
MIL Spec.	MS-3367-1
Other approval	BVQ

Ordering Information

Length (mm)	186
Width (mm)	4.8
Thickness (mm)	1.3
Max. Bundle Diameter (mm)	45
Min. Bundle Diameter (mm)	3.5
Min. Tensile Strength (N)	220
Quantity (pieces)	1000
Packaging Type	bag
Storage Conditions	Nylon (Polyamide) is inherently susceptible to environmental conditions. Polyamide 6.6 cable ties are moisturised to optimum performance levels at machine-side and should be stored in cool dry areas out of

Tooling

direct sunlight. Cable ties are packaged in plastic bags to contain moisture and should remain sealed until ready for use.

ERG50, ERG120, WT193A