

HEYCO



Heyco® Foam Washers

WILL FIT THESE ELECTRICAL TRADE SIZES	PART NO. Black	DESCRIPTION	PART DIMENSIONS					
			A Inside Dia.		B Outside Dia.		C Thickness	
			in.	mm.	in.	mm.	in.	mm.
.125" (3,2 mm) Thickness								
1/4	1970	HFW 500	.500	12,7	.820	20,8	.125	3,2
-	1971	HFW 625	.625	15,9	.940	23,9		
-	1972	HFW 750	.750	19,1	1.060	26,9		
1/2	1973	HFW 875	.875	22,2	1.185	30,1		
-	1974	HFW 1000	1.000	25,4	1.390	35,3		
3/4	1982	HFW 1125	1.125	28,6	1.515	38,5		
-	1983	HFW 1250	1.250	31,8	1.875	47,6		
1	1998	HFW 1375	1.375	34,9	2.000	50,8		
.190" (4,8 mm) Thickness								
1/4	1975	HFW 1/4	.480	12,2	.860	21,8	.190	4,6
1/2	1977	HFW 1/2	.840	21,3	1.200	30,5		
3/4	1978	HFW 3/4	1.050	26,7	1.500	38,1		
1	1979	HFW 1	1.300	33,0	1.700	43,2		

- For use with Heyco-Flex fittings.
- Provide additional degree of protection for a variety of fittings.
- Compensate for non-ideal mounting surfaces in application.

Heyco® Thermoplastic Rubber O-Rings

WILL FIT THESE ELECTRICAL TRADE SIZES	PART NO. Black	DESCRIPTION	PART DIMENSIONS					
			A Inside Dia.		B Outside Dia.		C Thickness	
			in.	mm.	in.	mm.	in.	mm.
1/2	1995	ROR 1/2	.860	21,8	1.140	28,9	.140	3,5
3/4	1996	ROR 3/4	1.050	26,7	1.320	33,5		
1	1997	ROR 1	1.300	32,9	1.570	39,9		

Consult Heyco for 1-1/4", 1-1/2" and 2" Electrical Trade Sizes.

- For use with Heyco-Flex fittings mounted in non-threaded holes.
- Liquid tight, dust tight and oil tight at enclosure.
- Suitable for wet locations requiring a separate gasket between the fitting and enclosure.
- Resistant to petroleum oil, mineral oil and grease, diesel fuel, weak acids, alkali, and salt solutions.

Material	HFW	EPDM
Material	ROR	Buna-N (Nitrile Rubber NBR)
Operating Temperature Range		-30°F (-34°C) to 212°F (100°C)
Maximum Temperature Rating		250°F (121°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1995](#) [1973](#) [1977](#) [F8426](#) [F8434](#)